

## Clamps



**Waterpipe Ground Clamps**



Cat. No.	Ground Wire Size	Water Pipe Size
<b>2-TB</b>	#6, #4, #2 AWG	1/2 in., 3/4 in., 1 or rebar 4-10
<b>3-TB</b>		1-1/4 in., 1-1/2 in. or 2 in.
<b>4</b>		2-1/2 in., 3 in. or 3-1/2 in.
<b>5-TB</b>		4 in., 4-1/2 in. or 5 in.
<b>6</b>		6 in.

Malleable iron crossbar, steel U-Bolt c/w copper cable clamp with serrations.



**Waterpipe Ground Clamps**



Cat. No.	Ground Wire Size	Water Pipe Size
<b>3902</b>	#4-4/0 AWG	1/2 in.-1
<b>3903</b>		1-1/4 in.-2 in.
<b>3904</b>		2-1/2 in.-3-1/2 in.
<b>3905-TB</b>		4 in.-5 in.
<b>3906-TB</b>		6 in.
<b>3907</b>		8 in.
<b>3908</b>		10 in.
<b>3909-TB</b>		12 in.

Material: Steel U-bolt and nut c/w bronzed aluminum cap and crossbar cadmium plated plus gold chromate finish.



**Waterpipe Ground Clamps**



Cat. No.	Ground Wire Size	Water Pipe Size
<b>3902BU*</b>	#4-4/0 AWG	1/2 in.-1
<b>3903BU*</b>		1-1/4 in.-2 in.
<b>3904BU*</b>		2-1/2 in.-3-1/2 in.
<b>3905BU*</b>		4 in.-5 in.
<b>3906BU*</b>		6 in.
<b>3907BU*</b>		8 in.
<b>3908BU*</b>		10 in.
<b>3909BU*</b>		12 in.

Material: Bronze U-bolt and nut c/w bronzed aluminum cap and crossbar with a brite dip finish. \*UL Listed for Direct Burial.



**3826**



**3840-TB**

### Ground Clamps



Cat. No.	Material	Water Pipe, Copper Tubing Size	Ground Rod Size
<b>3826*</b>	Malleable Iron	1/2 in., 3/4 in.	1/2 in.-1
<b>3846*</b>	Bronze		
<b>3840-TB*</b>	Malleable Iron	1/2 in., 3/4 in. or 1	

\* For unarmored copper wires #6, #4 AWG. UL approved for direct burial.  
 • #8 thru #4 AWG. Not CSA Certified



**3844**

For armored and unarmored wires.

### Ground Clamps for K&L Grade Copper Tubing Only



Cat. No.	Ground Wire Size	Water Pipe, Copper Tubing Size
<b>3844*</b>	#8-#4 AWG	1/2 in.-1
<b>3888**</b>		1/2 in.-1 also rebar 4-10

\* With Steel Screws.  
 \*\* UL approved for direct burial. Silicon Bronze Screws.



### Ground Clamp Accessories

Cat. No.	Description	For use with
<b>10102-TB</b>	1-1/4 to 1-1/2 in. cables	#8-#2 Ground wire

Material: Malleable iron, zinc plated.



Cat. No.	For use with
<b>10105</b>	Single conductors #4 solid to 2/0 str.
<b>10109</b>	Single conductors 2/0 solid to 4/0 str.