

OT400U03



OT400U03 SWITCH-DISCONNECTOR

General Information

Extended Product Type	OT400U03
Product ID	1SCA022747R6490
EAN	6417019242613
Catalog Description	OT400U03 SWITCH-DISCONNECTOR
Long Description	3-pole, front operated, base mounted non-fusible disconnect switch, handle and shaft are not included, terminal bolt kit included

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85365080

Popular Downloads

Data Sheet, Technical Information	1SCC301020C0201
Instructions and Manuals	1SCC301035M0019
Mechanical Drawings	1SCC301262F0002 1SCC301261F0002

Dimensions

Product Net Width	221 mm
Product Net Height	220 mm
Product Net Depth / Length	105 mm
Product Net Weight	3 kg 6.7 lb

Technical

Rated Operational Current AC-22A (I_e)	(380 ... 415 V) 400 A (500 V) 400 A (690 V) 400 A
Rated Operational Current AC-23A (I_e)	(380 ... 415 V) 400 A (500 V) 400 A (690 V) 400 A
Rated Operational Power AC-23A (P_e)	(380 ... 415 V) 220 kW (500 V) 280 kW (690 V) 400 kW

Conventional Thermal Current (I_{the})	Fully Enclosed 400 A
Rated Impulse Withstand Voltage (U_{imp})	12 kV
Rated Insulation Voltage (U_i)	acc. to IEC/EN 60664-1 1000 V
Rated Operational Voltage	Main Circuit 1000 V
Rated Short-Circuit Making Capacity (I_{cm})	(690 V) 65 kA
Rated Short-time Withstand Current (I_{cw})	for 1 s 15 kA
Power Loss	at Rated Operating Conditions per Pole 10 W
Pollution Degree	3
Handle Type	Handle and shaft not included
Switches Operating Mechanism	Mechanism at the End of the Switch 03 (Left Side)
Distance Between Phases	Standard
Position of Line Terminals	Top In - Bottom Out Bottom In - Top Out
Operating Mode	Front operated
Standards	IEC 60947-3 / UL 98 / CSA C22.2 NO.4
Special Functions	No
Mounting Type	Base mounting
Number of Poles	3
Terminal Type	Lug terminals
Tightening Torque	acc. IEC 60947-1 42.4 N·m

Technical UL/CSA

Maximum Operating Voltage UL/CSA	600 V
Horsepower Rating UL/CSA	(acc. to UL 200 V) 100 Hp (acc. to UL 208 V) 100 Hp (acc. to UL 240 V) 125 Hp (acc. to UL 480 V) 250 Hp (acc. to UL 600 V) 350 Hp
Ampere Rating UL/CSA	400 A
Tightening Torque UL/CSA	375 in·lb

Environmental

RoHS Status	Following EU Directive 2011/65/EU
Environmental Information	1SCC301149D0202

Certificates and Declarations (Document Number)

Declaration of Conformity - CE	1SCC301135D2704
Environmental Information	1SCC301149D0202
Instructions and Manuals	1SCC301035M0019
RoHS Information	1SCC301149D0203

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	250 mm 9.8 in

Package Level 1 Depth / Length	290 mm 11.4 in
Package Level 1 Height	170 mm 6.7 in
Package Level 1 Gross Weight	3.3 kg 7.3 lb
Package Level 1 EAN	6417019242613

Classifications

Object Classification Code	Q
ETIM 5	EC000216 - Switch disconnecter
ETIM 6	EC000216 - Switch disconnecter
ETIM 7	EC000216 - Switch disconnecter
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Low Voltage Products and Systems → Switches → Switch Disconnectors

