



TH4110D1007/U

PRO 5-2 Programmable Thermostat

Overview

The PRO programmable family of thermostats offers a basic thermostat with the benefits of energy savings. The PRO features an easy-to-read display and 5-2 day programming. Best of all, it's backed by the Honeywell name.

Features

- Weekday/Weekend programming - 5-2 (Weekdays, Weekend) programming
- Backlit digital display - both current and set temperatures are easy to read in various lighting conditions
- Precise comfort control [± 1 F (± 0.5 C)] - maintains consistent comfort to the highest level of accuracy
- Basic operation - easy-to-use slide switches allow you to select the heat or cool mode, and operate the fan
- the PRO 4000 has built in instructions - simple, pull out instruction manual
- Adaptive Intelligent Recovery™ - ensures programmed temperature is reached by programmed time

Product Specifications

Application	Heat/Cool or Heat Pump without Auxiliary Heat
Dimensions (in.)	3 13/16 in. High X 5 3/8 in. Wide X 1 1/4 in. Deep
Dimensions (mm)	97 mm High X 137 mm Wide X 32 mm Deep
Item Type	Product
Mounting	Horizontal
Electrical Ratings	20 to 30 Vac or 750 mV
Frequency	50 Hz; 60 Hz
Stages	1 Heat/1 Cool
Operating Humidity Range (% RH)	5 to 90% RH, non-condensing
Switch Positions (System)	HEAT-OFF-COOL
Switch Positions (Fan)	AUTO-ON
Sensor Element	Thermistor
Differential Temperature (F)	± 1 F
Differential Temperature (C)	± 0.5 C
Color	Premier White®
Programmability	5-2 Day Program
Power Method	Dual Powered: Battery or Hardwire
Terminal Designations	R, Rc, W, Y, G, O, B, C
Display Size	1.73 sq in.
Changeover	Manual
Setting Temperature Range (F)	Heat: 40 F to 90 F; Cool: 50 F to 99 F
Setting Temperature Range (C)	Heat: 4.5 C to 32 C; Cool: 10 C to 37 C
Cool Current	0.02 A to 1.0 A running

Heat Current

0.02 A to 1.0 A running