


Commercial-Grade HDMI® Cables

4K/18G Commercial-Grade HDMI Cables – CL3/FT4 UL Rated

4K/18G HDMI Cables, support HDR10, HDCP 2.2, Ethernet, ARC with Booster Tech - CL3/FT4 UL Rated

**BOOSTER
TECH**

KD-Pro30G	30 ft. HDMI Cable	24 AWG	
KD-Pro40G	40 ft. HDMI Cable	24 AWG	
KD-Pro50G	50 ft. HDMI Cable	24 AWG	
KD-Pro75G	75 ft. HDMI Cable	24 AWG	



Key Features

- > **4K/UHD Support:** 4096x2160 or 3840x2160 50/60Hz at 4:4:4
- > **18 Gbps Bandwidth:** High Speed / Performance for latest HDMI standards
- > **High Dynamic Range (HDR) Format Support:** HDR10 and Dolby® Vision
- > **HDCP 2.2:** Compliancy up to HDCP 2.2 and backward compliant
- > **Ethernet Channel:** 100 Mb/s Ethernet between two HDMI connecting devices
- > **Audio Return Channel:** Audio can be returned from display back to HDMI source for amplification and display
- > **Deep Color Support:** Up to UHD/4K 24/25/30Hz 4:4:4/12 bits or 50/60Hz 4:2:0/12 bit

- > **OPEN EYE™ Technology:** Certified & tested for low loss and noise-free performance

- > **Support All Digital Audio Formats:** Dolby® TrueHD, Dolby® Digital Plus, Dolby® Atmos and DTS-HD Master Audio™



HDMI
HIGH-DEFINITION MULTIMEDIA INTERFACE

HDMI is a registered trademark of HDMI Licensing, LLC. Dolby is a registered trademarks of Dolby Laboratories. DTS-HD Master Audio is a trademark of DTS, Inc.

Key digital

521 East 3rd Street • Mount Vernon, NY 10553 • Phone: 914.667.9700 • www.keydigital.com