



Rocelco 12U LCD Rack

Swing-Out Wall Mount Design & LCD Thermostat Control Panel

- ✓ ***Now with LCD Thermostat Control Panel to automatically set cooling fan start and stop temperature.***
- ✓ ***Conforms to all industry standards for 19" audio/video & server racks in 600x600mm configuration.***
- ✓ ***Assembled dimensions HWD 23.6" x 23.6" x 23.6". Max. load capacity 60kg/132 lbs.***
- ✓ ***Complete rack includes frame, all vertical & horizontal rails, front glass door, rear metal swing-out door, 2 side panels, 2 locks w/2 keys, 2 UL listed fans, assembly hardware & instructions (assembly instructions also on www.rocelco.com). Shelves not included.***
- ✓ ***Racks available fully assembled at extra cost.***
- ✓ ***Available shelves include 2U 16", 2U 18", 5U 20".***
- ✓ ***Other available accessories include 2U blank panels, Rocelco PDU (8-outlet power strip for racks) & Rocelco RCM (rack cable manager).***

