



# S29394

54W/LED/HID/5000K/100-277V/EX39  
54 watt - LED HID Replacement; 5000K; Mogul extended base;  
100-277 volts

### Features

- High Lumen Omni-directional LED for Industrial / Commercial applications
- Replaces HID, CFL, and Incandescent
- Ballast by-pass - Direct wire only 100V - 277V
- UL approved for totally enclosed fixtures
- Damp location - IP65 rated
- For outdoor & indoor use
- DLC Listed
- Base up or base down operation (high/low bay and post top)
- Emits no UV light / Contains no mercury (Hg)
- 5 year limited warranty
- Classified under UL 1598C

### Additional Technical Specifications

- Power Factor >0.9
- Operating temperature range -20°C to 65°C
- Operating Frequency 50-60Hz
- Working Voltage AC90-305V

Shatter resistant materials, acceptable for use in food prep areas



S29394

Minimum Compartment Size		
Length	Width	Depth
17.3 inch	9.25 inch	9.25 inch

Optional accessory: In-line surge protector [80-929](#)

Item Number	Product Line	UPC	Input Voltage	Watts	Operating Frequency	Incandescent Equivalent	Fluorescent Equivalent
S29394	Hi-Pro	045923293948	100 - 277	54	50/60Hz	300W	85W

HID Equivalent	Base	ANSI Base	Lamp Code		Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches
250W	Mogul Extended	EX39	54W/LED/HID/5000K/100-277V/EX39		Non-Dimmable	White	10-3/4"	3.69"
Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature		Pack
7200	50000	5000	Natural Light	80+	300	-20C (-4F) to a maximum of +65C (+149F)		12
Package Type	CEC Status	DLC ID:		RoHS Compliant	UL Classification		Warranty	
Box	Lawful for sale in California	PLGVDP7L3LM <a href="#">DLC Search</a>		Yes	cULus - Wet Location Rated		<a href="#">5 Year Limited</a>	



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

