

FSS 1500



FS Pipe/Conduit Seal 300-1500 2-1/2



Product image
not available

General Information

Extended Product Type	FSS 1500
Product ID	7TAA260080R0038
EAN	0783786725014
Catalog Description	FS Pipe/Conduit Seal 300-1500 2-1/2
Long Description	Flood Seal, Pipe/Conduit Seal, 300 - 1500 kcmil, .760 inch - 1.880 inch, 2-1/2 inch IPS. EPDM Rubber. (1) Cap, (1) Rocket, (4) Pack of Silicone Grease. Cap 5-23/64 inch long x 3 inch Diameter. Rocket 9-23/64 inch x 3 inch diameter.

Ordering

EAN	0783786725014
Minimum Order Quantity	1 piece

Dimensions

Product Net Weight	349.27 g
--------------------	----------

Container Information

Package Level 1 EAN	30034481009093
Package Level 2 Units	10 piece
Package Level 2 Width	244.475 mm
Package Level 2 Height	196.85 mm
Package Level 2 Depth / Length	355.6 mm
Package Level 2 EAN	50783786725019
Package Level 3 Depth / Length	25.4 mm

Additional Information

Brand / Label	Homac
Color	Black
Function	Watertight Splice Applications. Rated 600 Volts - built for Heavy-Duty Loads.
Material	Santoprene Rubber
Product Main Type	HOMAC UNDERGROUND CONNECTORS
Product Name	HOMAC-URD IN-LINE SPLICES&BUSC
Product Type	Insulating Cover - End Caps

Special Functions	Sizes for most conductors, perfect for Copper or Aluminum Conductors ranging from #14 AWG to 1500 kcmil. Easy to Install. Waterproof. Eliminate taping to significantly reduce labor and material cost of splice preparation.
Standards	RUS Accepted
UPC	783786725014

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	FSS 1500
Instructions and Manuals	FSS 1500

Classifications

UNSPSC	39121468
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4698 >> Input output connector cover

Categories

Low Voltage Products and Systems → Installation Products → Cable Accessories and Apparatus → Distribution Connectors



Product image
not available