

# AC336



AL 10IN TENSION COMP SPLICE 336.4



## General Information

Extended Product Type	AC336
Product ID	7TAA267220R0006
EAN	0783786037780
Catalog Description	AL 10IN TENSION COMP SPLICE 336.4
Long Description	Aluminum 10 inch Full-Tension Distribution Compression Splice for Wire Range: 336.4 (19, 37), Hydraulic Dies: B80EA, 321, 1 1/8-1

## Ordering

EAN	0783786037780
Minimum Order Quantity	20 piece
Customs Tariff Number	8536904000

## Dimensions

Product Net Weight	218.588 g
--------------------	-----------

## Container Information

Package Level 1 EAN	30783786051022
Package Level 2 Units	20 piece
Package Level 2 Width	165.1 mm
Package Level 2 Height	111.76 mm
Package Level 2 Depth / Length	375.92 mm
Package Level 2 EAN	50783786037785

## Additional Information

Brand / Label	Blackburn
Function	Distribution Compression Connector
Insulation Material	None
Material	Aluminum
Mounting Type	None
Product Main Type	BLACKBURN OVERHEAD CONNECTORS
Product Name	BKB-OVERHEAD SPLICE & TAP CONN
Product Type	Compression Connector / Splice

Special Functions	Center stop assures proper conductor positioning. External end taper provides conductor stress relief, ease of stringing and corona protection. Internal end chamfer allows easy conductor insertion and prevents sharp edge contact with conductor.
Standards	ANSI C119.4
UPC	783786037780

---

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information	AC336
Instructions and Manuals	AC336

---

### Classifications

UNSPSC	39121449
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4669 >> Wire or cable compression splice

---

### Categories

Low Voltage Products and Systems → Installation Products → Cable Accessories and Apparatus → Distribution Connectors

