

AC2-TB



AL 4-1/8IN TENSION COMP SPLICE 4



General Information

Extended Product Type	AC2-TB
Product ID	7TAA267220R0001
EAN	5415022348361
Catalog Description	AL 4-1/8IN TENSION COMP SPLICE 4
Long Description	Aluminum 4-1/8 inch Full-Tension Distribution Compression Splice for Wire Range: 4(7), Mechanical Dies: BY23, W-163, 1/2, Hydraulic Dies: B17EA, 163, 1/2, 510

Ordering

EAN	5415022348361
Minimum Order Quantity	25 piece
Customs Tariff Number	8536904000

Dimensions

Product Net Weight	28.939 g
--------------------	----------

Container Information

Package Level 1 Units	25 piece
Package Level 1 Width	83.82 mm
Package Level 1 Height	134.62 mm
Package Level 1 Depth / Length	137.16 mm
Package Level 1 EAN	30783786051022
Package Level 2 Units	250 piece
Package Level 2 EAN	50783786051026

Additional Information

Brand / Label	Blackburn
Function	Distribution Compression Connector
Insulation Material	None
Material	Aluminum
Mounting Type	None
Product Main Type	BLACKBURN OVERHEAD CONNECTORS
Product Name	BKB-OVERHEAD SPLICE & TAP CONN

Product Type	Compression Connector / Splice
Special Functions	Center stop assures proper conductor positioning. External end taper provides conductor stress relief, ease of stringing and corona protection. Internal end chamfer allows easy conductor insertion and prevents sharp edge contact with conductor.
Standards	ANSI C119.4
UPC	783786051021

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	AC2-TB
Instructions and Manuals	AC2-TB

Classifications

UNSPSC	39121449
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4669 >> Wire or cable compression splice

Categories

Low Voltage Products and Systems → Installation Products → Cable Accessories and Apparatus → Distribution Connectors

