



Representative

Catalog Number: RC20
Product ID: 7TAA267310R0001
UPC Number: 78378605121
Status: Active

Aluminum 16 inch Full-Tension Distribution Compression Splice for Wire Range: 2/0 AC-SR(6/1), 2/0 AAAC(7), 2/0 5005(7), 2/0 AAC(7), Mechanical Dies: 781, Hydraulic Dies: B74AH, 659, 3/4

North American Specifications (UNSPSC)

| | |
|----------------------|---|
| UNSPSC | 39121449 Wire or cable compression splice |
| IGCC | 4669 Wire or cable compression splice |
| Brand Name | Blackburn |
| Type | Compression Connector / Splice |
| Special Features | Center stop assures proper conductor positioning. External end taper provides conductor stress relief, ease of stringing and corona protection. Internal end chamfer allows easy conductor insertion and prevents sharp edge contact with conductor. Replaces two-piece splices. Type RC Single Sleeve, Full Tension Splice for ACSR, AAAC, 5005 and AAC Conductor. |
| Application | Distribution Compression Connector |
| Standard | ANSI C119.4 |
| Size | 16 inch |
| Connection | compression |
| Conductor Range | Wire Range: 2/0 ACSR(6/1), 2/0 AAAC(7), 2/0 5005(7), 2/0 AAC(7) |
| Number Of Conductors | 2 |
| Material | Aluminum |
| Insulation | None |
| Mounting | None |

Packaging

| | |
|---------------------------|--------------------|
| Outer Quantity | 25 |
| Outer Dimensions (inches) | 17.4x6.4x5 |
| Weight Uom | 58.13 lbs. per 100 |

Documents / Support Tools

| | |
|----------|---------------|
| SDS US 1 | sds-00054-tb2 |
|----------|---------------|

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com