


LTGUS03G-C



LFMC GP UL 3/4IN GRY 30M/100FT



General Information

Extended Product Type	LTGUS03G-C
Product ID	7TAA012LN0R0002
EAN	5415022391152
Catalog Description	LFMC GP UL 3/4IN GRY 30M/100FT
Long Description	Liquid Tight Flexible Metallic Conduit, General Purpose, Galvanised Steel Core with PVC Jacket, Conduit Size 3/4 Inch, Length 30 Meters/100 Feet, Working Temperature -30 to 80 Degrees C, UL E125517, CSA LR-72635, Compliant to RoHS, Gray

Ordering

EAN	5415022391152
Minimum Order Quantity	100 piece
Customs Tariff Number	8307106000

Dimensions

Product Net Weight	191.282 g
--------------------	-----------

Container Information

Package Level 1 EAN	30786210828894
Package Level 2 Units	100 piece
Package Level 2 Width	517.652 mm
Package Level 2 Height	203.2 mm
Package Level 2 Depth / Length	527.05 mm
Package Level 2 EAN	00786210108421

Additional Information

Brand / Label	T&B Conduit
Color	Gray
Function	General Purpose
Material	Galvanised Steel
Product Main Type	T&B LIQUIDTIGHT
Product Name	Flex conduit of steel w/o fittings
Product Type	Liquid Tight Flexible Metallic Conduit

Special Functions	High quality cores and jackets for excellent strength and durability
Standards	UL E125517, CSA LR-72635, RoHS
UPC	786210108421

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TDS000117
Instructions and Manuals	LTGUS03G-C

Classifications

ETIM 6	EC001179 - Protective metallic hose
ETIM 7	EC001179 - Protective metallic hose
UNSPSC	39131706
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5543 >> Liquid Tight Conduit

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Liquidtight Fittings

