



## Service Entrance Splices

**T&B Catalog Number:**

TR65

**UPC Number:**

78378610148

**Status:**

Active

**Description:**

Aluminum 6" Service Entrance Compression Splice for Wire Range 1 AS-CR, 1/0 Str., Yellow, Die: 5/8

### Features

Triplex Neutral Splice with semi-tension.

Color-coded and marked for easy identification.

### General

Insulation Type	Non-Insulated
Material	Aluminum
Barrel Length	Longer Length
Conductor Range A ASCR	1
Conductor Range A Str./Sol.	1/0 Str.
Conductor Range B Str./Sol.	-
Conductor B Color	Yellow

### Dimension Information

Length (inches)	6
Conductor A Diameter Max.	0.373
Conductor A Diameter Min.	0.355

### Tooling

Die Series	5/8" Die Series
Mechanical Dies	5/8 (OD58 Tool) Peach, G, TU

### Packaging

T&B Inner Pack	50
Package in Units	300
T&B Sold in UOM	Each
T&B Weight Per UOM	13 lbs. per 100

### Notes

Decimal dimensions are for conventional conductor, not Copperweld or Alumoweld.

### Certifications

RoHS Compliance	Yes
-----------------	-----

#### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: techsupport@tnb.com