

CIRKA - CRK

SURFACE MOUNT LED FIXTURE

CIRKA is a LED ceiling and wall surfaced mount utilizing up-to-date LED technology in a lightweight slim housing. It provides highly efficient illumination that is perfectly suited for new surfaced installations solutions. Typical applications include hallways, bathrooms and closets.

FEATURES AND SPECIFICATIONS

• Construction

Housing

Housing comes standard in white with an anti-corrosive paint finish. Screwless magnetic trims available in five colour. See accessories table below.

Mounting

Surface and ceiling mount.

Applications

- Residential
- Office
- Commercial
- Hospitality


• Technical specifications

- Long life LEDs that provide 80+ CRI are available in 3000K and 4000K colour temperature
- Estimated lifespan of over 90,000 hours to L70
- Triac dimming is standard
- Suitable for damp locations
- Operating temperature: -20°C to +40°C
- Storage temperature: -40°C to +85°C

• Compliances

- Meets requirements of ICES-005 (B)
- cETLus
- Energy Star certified

DIMENSIONS



Part number	Size	Housing diameter	Optical diameter	Housing thickness
CRK-5	5"	5.31"	3.69"	0.5"
CRK-7	7"	7.06"	5.44"	0.5"
CRK-9	9"	8.88"	7.25"	0.5"
CRK-12	12"	11.81"	10.19"	0.5"

COMPATIBLE DIMMERS

Brand	Model number	Brand	Model number
Lutron	DVW-603PGH-WH	Leviton	DSL06-1LZ
Lutron	MACL-153MR-WH	Leviton	6674-POW
Leviton	6672-1LW	Lutron	PD-6WCL-WH
Lutron	SCL-153P-WH	Lutron	CTCL-153P-WH
Leviton	IPL06-10Z	Lutron	MSCL-OP153M-WH
GE	45857GR	Lutron	DVCL-153P-WH

Project: _____
 Type: _____
 Catalogue #: _____
 Drawn by: _____
 Date: _____



OVERVIEW

Light source	LED
Wattage	6W - 24W
Lumens	400lm - 2000lm
lm/W	65 lm/W - 85 lm/W
Colour temperature	3000K, 4000K
CRI	80+
Weight	0.4 lbs, 0.6 lbs, 0.88 lbs, 1.4 lbs

QUICK SHIP ORDERING GUIDE


Part number	Size	Lumens	Wattage	Voltage	Colour temperature
CRK-5-30-1	5"	400lm	6W	120V	3000K
CRK-5-40-1	5"	400lm	6W	120V	4000K
CRK-7-30-1	7"	1000lm	12W	120V	3000K
CRK-7-40-1	7"	1000lm	12W	120V	4000K
CRK-9-30-1	9"	1500lm	18W	120V	3000K
CRK-9-40-1	9"	1500lm	18W	120V	4000K
CRK-12-30-1	12"	2000lm	24W	120V	3000K
CRK-12-40-1	12"	2000lm	24W	120V	4000K

* **QUICK SHIP:** Product availability is subject to change without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.

LUMEN AND SPECIFICATION CHART

General specifications										Lumen maintenance
Package	Input voltage (V)	LED current (A)	System power (W)	Lumens	LM/W	CCT	CRI	PF	THD	Calculated TM21 @ 55°C
CRK-5-30-1	120 V	55 mA	6W	400lm	65 lm/W	3000K	80+	> 90%	< 40%	90,000
CRK-5-40-1	120 V	55 mA	6W	400lm	65 lm/W	4000K	80+	> 90%	< 40%	90,000
CRK-7-30-1	120 V	110 mA	12W	1000lm	80 lm/W	3000K	80+	> 90%	< 40%	90,000
CRK-7-40-1	120 V	110 mA	12W	1000lm	80 lm/W	4000K	80+	> 90%	< 40%	90,000
CRK-9-30-1	120V	170 mA	18W	1500lm	80 lm/W	3000K	80+	> 90%	< 40%	90,000
CRK-9-40-1	120V	170 mA	18W	1500lm	80 lm/W	4000K	80+	> 90%	< 40%	90,000
CRK-12-30-1	120V	220 mA	24W	2000lm	85 lm/W	3000K	80+	> 90%	< 40%	90,000
CRK-12-40-1	120V	220 mA	24W	2000lm	85 lm/W	4000K	80+	> 90%	< 40%	90,000

SCREWLESS MAGNETIC TRIMS



ACCESSORIES (order separately)

RNG-TRM05-BN	5" Brushed nickel trim
RNG-TRM07-BN	7" Brushed nickel trim
RNG-TRM09-BN	9" Brushed nickel trim
RNG-TRM12-BN	12" Brushed nickel trim
RNG-TRM05-BK	5" Polished Black trim
RNG-TRM07-BK	7" Polished Black trim
RNG-TRM09-BK	9" Polished Black trim
RNG-TRM12-BK	12" Polished Black trim
RNG-TRM05-PC	5" Polished Chrome trim
RNG-TRM07-PC	7" Polished Chrome trim
RNG-TRM09-PC	9" Polished Chrome trim
RNG-TRM12-PC	12" Polished Chrome trim
RNG-TRM05-BRG	5" Brushed Rose Gold trim
RNG-TRM07-BRG	7" Brushed Rose Gold trim
RNG-TRM09-BRG	9" Brushed Rose Gold trim
RNG-TRM12-BRG	12" Brushed Rose Gold trim
RNG-TRM05-BB	5" Brushed Bronze trim
RNG-TRM07-BB	7" Brushed Bronze trim
RNG-TRM09-BB	9" Brushed Bronze trim
RNG-TRM12-BB	12" Brushed Bronze trim
Other colour upon request*	
RNG-TRM05-SN	5" Sand Nickel trim
RNG-TRM07-SN	7" Sand Nickel trim
RNG-TRM09-SN	9" Sand Nickel trim
RNG-TRM12-SN	12" Sand Nickel trim


* Minimum quantity required of 500.

Comments

PHOTOMETRIC DATA

CRK-5-30-1 • 358.9lm


Polar candela distribution



Zonal lumen summary


Zone	Lumens	% Fixture
0-30	110	30.6%
0-40	177.9	49.6%
0-60	299.5	83.5%
60-90	59.4	16.5%
70-100	24.2	6.7%
90-120	0	0%
0-90	358.9	100%
90-180	0	0%
0-180	358.9	100%

Illuminance at a distance



CRK-7-30-1 • 988.5lm


Polar candela distribution



Zonal lumen summary


Zone	Lumens	% Fixture
0-30	285.5	28.9%
0-40	464.4	47%
0-60	801.1	81%
60-90	187.4	19%
70-100	75.6	7.7%
90-120	0	0%
0-90	988.5	100%
90-180	0	0%
0-180	988.5	100%

Illuminance at a distance



CRK-9-30-1 • 1795.4lm

Polar candela distribution



Zonal lumen summary

Zone	Lumens	% Fixture
0-30	476.3	26.5%
0-40	784.4	43.7%
0-60	1397.9	77.9%
60-90	395.8	22%
70-100	173.6	9.7%
90-120	1.4	0.1%
0-90	1793.6	99.9%
90-180	1.8	0.1%
0-180	1795.4	100%

Illuminance at a distance

