



The unfailing choice for lasting confidence

Investing in quality pays off in the long run.

- Help bolster wellbeing and productivity without worrying about flicker and other undesired effects.
- Immerse users in comfortable, welcoming spaces that are free of glare and distractions; with color that remains consistent across luminaires and over time.
- Protect both the integrity of electrical equipment and overall building efficiency from the effects of total harmonic distortion.
- Rely on one flat panel LED luminaire family for multiple applications - recessed, surface, or suspended.

Affordable

doesn't
have to
mean cheap



Why risk the unknown, and your reputation, for the sake of short-term savings?

FluxPanel luminaires are specially designed to keep your budget on track, and unlike others, we don't stop there. Backed by more than 125 years of Philips Lighting expertise, each low-profile, dimmable LED luminaire imparts confidence and peace of mind for you and those in the space.

Reliable **Philips Advance drivers** offer dependable and lasting performance, while the low glare surface gradient creates uniform light distribution.

FluxPanel luminaires are well-suited for office, healthcare and educational facilities that seek to minimize hassles, meet sustainability goals, and maximize return on investment.

When a good deal matters, put your trust in FluxPanel luminaires. Visit www.philips.com/fluxpanel.

FluxPanel LED luminaire

Ordering guide – Standard configurations available with all choices, unless otherwise noted. Base configurations selections indicated by blue.

Example: 2FXP38L840-2-DS-UNV-DIM-EMLED7

| Width | Family | Nominal delivered lumens | Color | Length | Diffuser | Voltage | Driver | Options ² |
|----------------------|------------|--------------------------------|-----------------------------|------------------------|-------------------------------|---|--|---|
| <input type="text"/> | FXP | <input type="text"/> | <input type="text"/> – | <input type="text"/> – | DS – | <input type="text"/> – | <input type="text"/> – | <input type="text"/> |
| 1 1' | FXP | Standard configurations | 835 80 CRI, 3500K | 2 2' | DS Diffuse (smooth) | UNV Universal Voltage, 120-277 volt | DIM' 0-10V dimming | F1 3/8" flex, 3 wire 18 gauge 6' |
| 2 2' | | 2x2 | 840 80 CRI, 4000K | 4 4' | | 347 347V | SDIM Step dimming to 40% input power | F2 3/8" flex, 4 wire 18 gauge 6' |
| | | 30L 3000 lumens | | | | | XDIM MarkX phase dimming | F1/D 3/8" twin flex, 3 wire 18 gauge 6' for dimmable luminaires |
| | | 38L 3800 lumens | | | | | | F2/5W 3/8" single flex, 5 wire 18 gauge 6' for dimmable luminaires |
| | | 45L 4500 lumens | | | | | | F2/6W 3/8" single flex, 6 wire 18 gauge 6' for dimmable and emergency luminaires |
| | | 2x4 | | | | | | GLR Fusing, fast blow |
| | | 38L 3800 lumens | | | | | | EMLED Bodine BSL310 10W battery pack |
| | | 43L 4300 lumens | | | | | | EMLED7 Bodine BSL17 7W battery pack |
| | | 48L 4800 lumens | | | | | | CHIC Chicago Plenum rated |
| | | 54L 5400 lumens | | | | | | |
| | | 60L 6000 lumens | | | | | | |
| | | 1x4 | | | | | | |
| | | 30L 3000 lumens | | | | | | |
| | | 38L 3800 lumens | | | | | | |
| | | 45L 4500 lumens | | | | | | |
| | | Base configurations | | | | | | |
| | | 2x2 | | | | | | |
| | | 38B 3800 lumens | | | | | | |
| | | 2x4 | | | | | | |
| | | 42B 4200 lumens | | | | | | |
| | | 1x4 | | | | | | |
| | | 38B 3800 lumens | | | | | | |

Accessories (order separately)

- **FMA22** – 2'x2' "F" mounting frame for NEMA "F" mounting
- **FSK22** – 2'x2' surface mount field installation kit
- **FMA24** – 2'x4' "F" mounting frame for NEMA "F" mounting
- **FSK24** – 2'x4' surface mount field installation kit
- **FMA14** – 1'x4' "F" mounting frame for NEMA "F" mounting
- **FSK14** – 1'x4' surface mount field installation kit
- **2PCH48-1-SC** – adjustable cable hanger kit for 2x2 with straight white 18/3 cord (two-1 powered, 1 non-powered)
- **2PCH48-1D-SC** – adjustable cable hanger kit for 2x2 with straight white 18/5 cord for dimming (two-1 powered, 1 non-powered)
- **4PCH48-1-SC** – adjustable cable hanger kit for 1x4 or 2x4 with straight white 18/3 cord (two-1 powered, 1 non-powered)
- **4PCH48-1D-SC** – adjustable cable hanger kit for 1x4 or 2x4 with straight white 18/5 cord for dimming (two-1 powered, 1 non-powered)

Philips drivers provide reliable performance for peace of mind.



Footnotes

- 1 0-10v dimming to 1% for Standard, and 5% for Base configurations
- 2 All options available with Standard configurations only

FluxPanel luminaires are Designlights Consortium[®] qualified. Please see the DLC QPL list for exact catalog numbers (<http://www.designlights.org/QPL>).



© 2017 Philips Lighting Holding B.V. All rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.



Philips Lighting North America Corporation
200 Franklin Square Drive, Somerset, NJ 08873
Tel. 855-486-2216

Philips Lighting Canada Ltd.
281 Hillmount Rd, Markham, ON, Canada L6C 2S3
Tel. 800-668-9008