

Indoor Commercial

Catalogue no.	Size	Lamp/Watts	Voltage	Ballast	Service Quantity		Appl. Page
					2 days	10 days	

Surface Continued

Commercial Wrap

CFW232-120-1/2EB-GENIS	6-1/2"x48"	2-T8/32	120	T8 ELECT.	100		
------------------------	------------	---------	-----	-----------	-----	--	--

Designer Wrap

DPW232-UNV-1/2EB-GENIS	8"x48"	2-T8/32	120/277	T8 ELECT.	50		
------------------------	--------	---------	---------	-----------	----	--	--

Strips

Surface T5 Strip SV Series

SV2S114UNVPG	2"x22-1/2"	1-T5/14	120/277	T5 ELECT.	35		
SV2S124UNVPG	2"x22-1/2"	1-T5/14	120/277	T5 ELECT.	35		
SV3S121UNVPG	2"x34-1/4"	1-T5/21	120/277	T5 ELECT.	35		
SV3S139UNVPG	2"x34-1/4"	1-T5HO/39	120/277	T5HO ELECT.	35		
SV4S128UNVPG	2"x46"	1-T5/28	120/277	T5 ELECT.	100		
SV4S154347PG	2"x46"	1-T5HO/54	347	T5HO ELECT.		50	
SV4S154UNVPG	2"x46"	1-T5HO/54	120/277	T5HO ELECT.	100		18
SV4S228UNVPG	2"x46"	2-T5/28	120/277	T5 ELECT.	75		
SV4S254UNVPG	2"x46"	2-T5HO/54	120/277	T5HO ELECT.	50		18
SV4S254347PG	2"x46"	2-T5HO/54	347	T5HO ELECT.	50		
SV8S254UNVPV	2"x92"	4-T5HO/54	120/277	T5HO ELECT.		50	
SV8S254347PV	2"x92"	4-T5HO/54	347	T5HO ELECT.		50	

T5 SV Series Accessories

SV5GXG4	Wireguard for T5 SV Series				50		
SV5RIW4ASLD	Asymmetric Solid White Reflector				50		
SV5LWW4SSLD	Symmetric Solid White Reflector				70		
SV5FLW4SSLT	Symmetric Slotted Frosted Lens				70		
SV5RIW4SSLD	Symmetric Solid White Reflector				70		
SV5RIS4SSLD	Symmetric Solid Silver Reflector				70		

N Series Strip - Formerly Surface T8 Strip SB Narrow Series - See Cross Reference Guide (Page 10)

N117-UNV-1/1-EB	2-1/2"x24"	1-T8/17	120/277	T8 ELECT.	100		
N125-UNV-1/1-EB	2-1/2"x36"	1-T8/25	120/277	T8 ELECT.	100		
N125-347-1/1-EB	2-1/2"x36"	1-T8/25	347	T8 ELECT.		50	
N132-UNV-1/1-EB	2-1/2"x48"	1-T8/32	120/277	T8 ELECT.	80		18
N132-347-1/1-EB	2-1/2"x48"	1-T8/32	347	T8 ELECT.	100		
TN132-347-1/2-EB	2-1/2" x 96"	1-T8/32	347	T8 ELECT.	100		
TN132-UNV-1/2-EB	2-1/2"x96"	2-T8/32	120/277	T8 ELECT.	150		

T Series Strip - Formerly Surface T8 Strip SB Wide Series - See Cross Reference Guide (Page 10)

T232-UNV-1/2-EB	4-1/8"x48"	2-T8/32	120/277	T8 ELECT.	80		18
T232-347-1/2-EB	4-1/8"x48"	2-T8/32	347	T8 ELECT.	80		
TT232-UNV-1/4-EB	4-1/8"x96"	4-T8/32	120/277	T8 ELECT.	80		18
TT232-347-1/4-EB	4-1/8"x96"	4-T8/32	347	T8 ELECT.	80		
T296-120-1/2-EB	4-1/8"x96"	2-T8/59	120	T8 ELECT.	50		

