

Inground/ Ingrade - Line Voltage - continued

783352007247	IT236-H	120V / 12V, 75W PAR 36, Small Inground w/Composite Trim Ring, Bronze	✓✓		C
783426020868	IT236-N	120V / 12V, 75W PAR 36, Small Inground w/Cast Bronze Trim Ring, Natural Brass	✓✓		C
783427020874	IT236-SS	120V / 12V, 75W PAR 36, Small Inground w/Stainless Steel Trim Ring, Stainless Steel	✓✓		C
---	I25CRGN	External Cast Bronze Rock Guard (i2.5), Natural Brass		✓✓	
---	I35CRGN	Rock Guard (i3.5), Natural Brass		✓✓	

Inground/ Ingrade - Line Voltage Accessories

783352005625	CP3	Concrete Pour Kit (I3)	✓✓		C
783395020555	CPS3	Stainless Steel Concrete Pour Kit (I3), Stainless Steel	✓✓		C
783352006745	I3-HHO	I3-H Housing Only, Bronze	✓✓		C
783421020818	IS3H	I3 External Glare Shield	✓✓		C
---	CPS35	Stainless Steel Concrete Pour Kit (i35)		✓✓	
---	MA5	Mounting Compound for I4		✓✓	
783352005632	CP4	Concrete Pour Kit (I4)	✓✓		C
783396020561	CPS4	Stainless Steel Concrete Pour Kit (I4)	✓✓		C
783352006776	I4-HHO	I4,Housing Only, Bronze	✓✓		C
783352007193	IS4H	Shield	✓✓		C
---	CPS25 •	Stainless Steel Concrete Pour Kit (i2.5), Stainless Steel		✓✓	
---	CPS15	Concrete Pour Kit (i1.5)		✓✓	



Inground/ Ingrade - Low Voltage

UPC CODE	CATALOG NUMBER	DESCRIPTION	SERVICE SMART	SPEC SMART	STOCKED IN
783352006707	I2-H •	120V, 100W R30, Small Inground with Bronze Trim Ring, Bronze	✓✓		C
783352015617	I2-N	120V, 100W R30, Small Inground with Cast Bronze Trim Ring, Natural Brass	✓✓		C
783407020672	I2-SS	120V, 100W R30, Small Inground with Stainless Steel Trim Ring, Stainless Steel	✓✓		C
783352000125	IL116G-H	12V, 75W MR16, Inground w/Guard, Bronze	✓✓		C
783415020756	IL116G-N •	12V, 75W MR16, Composite Inground with Cast Bronze Rock Guard, Natural Brass	✓✓		C
783352000132	IL116-H	12V, 75W MR16, Inground, Bronze	✓✓		C
783416020762	IL116-N	12V, 75W MR16, Composite Inground with Cast Bronze Trim Ring, Natural Brass	✓✓		C
783417020778	IL116-SS	12V, 75W MR16, Composite Inground with Stainless Steel Trim Ring, Stainless Steel	✓✓		C
783352007032	IL136G-H	12V, 75W PAR 36, Inground w/Guard, Bronze	✓✓		C
783418020784	IL136G-N	12V, 75W PAR 36, Composite Inground with Cast Bronze Rock Guard, Natural Brass	✓✓		C
783352007049	IL136-H	12V, 75W PAR 36, Inground, Bronze	✓✓		C
783419020790	IL136-N	12V, 75W PAR 36, Composite Inground with Cast Bronze Trim Ring, Natural Brass	✓✓		C
783420020802	IL136-SS	12V, 75W PAR 36, Composite Inground with Stainless Steel Trim Ring, Stainless Steel	✓✓		C
783352000149	IL336-A •	12V, 50W PAR 36, Well Light, Black	✓✓		C
783352007070	IL336-ABULK25	12V, 50W PAR 36, Well Light, Bulk Pack 25, Black	✓✓		C
783352000156	IL336-AL •	12V, 20W PAR 36, Well Light w/Lamp, Black	✓✓		C
783352002143	IL336-ALBULK25	12V, 20W PAR 36, Well Light w/Lamp, Bulk Pack 25, Black	✓✓		C
783352007254	IUL516-H	12V, 35W MR16, Ultem Micro Inground, MR16, Bronze	✓✓		C
783352007261	IUL516-HBAB	12V, 20W MR16, Ultem Micro Inground, MR16, w/Lamp, Bronze	✓✓		C
783352002167	IUL516-HBULK25	12V, 35W MR16, Ultem Micro Inground, MR16, Bulk Pack 25, Bronze	✓✓		C

Inground/ Ingrade - Low Voltage Accessories

---	IBLR	Internal Ice Blue Lens (for i15 / i25)		✓✓	
---	ICGR	Internal Honeycomb Louver (for i15 / i25)		✓✓	
---	ILSLR	Internal Linear Spread Lens (for i25 / i25)		✓✓	
---	IMSLR	Internal Multi-Directional Spread Lens (for i15 / i25)		✓✓	
---	LEDADP	LED Accessory Adaptor Ring		✓✓	
783352000392	CP2 •	Concrete Pour Kit (I2)	✓✓		C
783394020549	CPS2	Stainless Steel Concrete Pour Kit (I2), Stainless Steel	✓✓		C
783352000477	IS1H	Inground Shield (for Mini Inground)	✓✓		C
783352000446	IG30H	Rock Guard w/o Lens (for IL336 Wellyte)	✓✓		C
783352000453	IG3H •	Rock Guard w/Lens (for IL336 Wellyte)	✓✓		C
783352000460	IL3H •	Lens Guard (for IL336 Wellyte)	✓✓		C

C= Carrollton, Texas

•" beside a blue catalog number indicates item is a recommended distributor shelf stock item.

Pictures are representative of product categories and may not illustrate the exact products listed on the pages of this guide.

Product information may change without notice. Contact your local Philips sales representative for additional product information.