





















Project: _____

Fixture Type: _____

Location: _____

Contact/Phone: _____

Trim Series	Dimensions	Aperture	Catalog No.		Housing/ Lamp Compatibility
 Gimbal Ring in Baffle	 7 5/8"	5-3/4"	224 BWH 224 WWH	6" Adjustable Gimbal Ring in Baffle Trim - Black Baffle, White Trim Ring 6" Adjustable Gimbal Ring in Baffle Trim - White Baffle, White Trim Ring	IC2: 75W PAR38 TC2/TC2R: 150W PAR38, 120W BR40 APT2: 150W PAR38, 120W BR40
 Cylinder Spotlight in Baffle	 7 5/8"		226 BWH 226 WWH	6" Adjustable Cylinder Spotlight in Baffle Trim - Black Baffle, White Trim Ring 6" Adjustable Cylinder Spotlight in Baffle Trim - White Baffle, White Trim Ring	IC2/TC2/TC2R: 60W PAR16 IC22/IC22 W/IC22 S/IC22R: 60W PAR16 IC23/IC23 W: 60W PAR16 APT2: 60W PAR16
 R/ PAR20 Regressed Eyeball	 8"		228 WH	6" Adjustable Regressed Eyeball Trim - White	IC2/TC2/TC2R: 50W PAR20, 50W R20 IC21/IC21R: 50W PAR20, 50W R20 IC22/IC22 W/IC22 S/IC22R: 50W PAR20, 50W R20 IC23/IC23 W: 50W PAR20, 50W R20 APT2: 50W PAR20, 50W R20
 R/PAR20 Regressed Eyeball in Baffle	 7 5/8"		248 WWH	6" Adjustable Regressed Eyeball in Baffle Trim - White Baffle, White Trim Ring	IC2/TC2/TC2R: 50W PAR20, 50W R20 IC21/IC21R: 50W PAR20, 50W R20 IC22/IC22 W/IC22 S/IC22R: 50W PAR20, 50W R20 IC23/IC23 W: 50W PAR20, 50W R20 APT2: 50W PAR20, 50W R20
 PAR/ BR30 Regressed Eyeball	 8"		229 ABZ 229 BL 229 SC 229 WH	6" Adjustable Regressed Eyeball Trim - Classic Aged Bronze 6" Adjustable Regressed Eyeball Trim - Black 6" Adjustable Regressed Eyeball Trim - Satin Chrome 6" Adjustable Regressed Eyeball Trim - White	IC2/TC2/TC2R: 75W PAR30L, 65W BR30 IC21/IC21R: 75W PAR30L, 65W BR30 IC22/IC22 W/IC22 S/IC22R: 75W PAR30L, 65W BR30 IC23/IC23 W: 50W PAR20, 50W R20 APT2: 75W PAR30, 75W PAR30L, 65W BR30
 PAR/ BR30 Regressed Eyeball in Baffle	 7 5/8"		249 BWH 249 WWH	6" Adjustable Regressed Eyeball in Baffle Trim - Black Baffle, White Trim Ring 6" Adjustable Regressed Eyeball in Baffle Trim - White Baffle, White Trim Ring	IC2/TC2/TC2R: 75W PAR30L, 65W BR30 IC21/IC21R: 75W PAR30L, 65W BR30 IC22/IC22 W/IC22 S/IC22R: 75W PAR30L, 65W BR30 IC23/IC23 W: 50W PAR20, 50W R20 APT2: 75W PAR30, 75W PAR30L, 65W BR30
 Low Voltage Pinhole with Baffle	 7 5/8" Adjustment: 30° Vertical, 358° Rotation	3-1/2"	424 BWH	6" Adjustable Pinhole with Baffle Trim - Black Baffle, White Trim Ring	IC2: 35W MR16 TC2/TC2R: 50W MR16 APT2: 50W MR16
 Low Voltage Cylinder Spotlight in Baffle	 7 5/8" Adjustment: 45° Vertical, 358° Rotation		427 WWH	6" Adjustable Cylinder Spotlight in Baffle Trim - White Baffle, White Trim Ring	IC2/TC2/TC2R: 50W MR16 APT2: 50W MR16
 PAR30 Adjustable Tapered Baffle	 7 5/8"	5-3/4"	264 WWH 264 BWH	6" Adjustable Tapered Baffle Trim - White Baffle, White Trim Ring 6" Adjustable Tapered Baffle Trim - Black Baffle, White Trim Ring	IC2/TC2/TC2R: 75W PAR30 IC22/IC22 W/IC22 S/IC22R: 50W PAR30 IC23/IC23 W: 50W PAR30 APT2: 75W PAR30
 PAR30 Adjustable Tapered Cone	 7 5/8"	5-3/4"	267 CWH 267 GWH 267 BWH 267 HZWH 267 WHZWH	6" Adjustable Tapered Cone Trim - Clear Alzak® Cone, White Trim Ring 6" Adjustable Tapered Cone Trim - Gold Alzak® Cone, White Trim Ring 6" Adjustable Tapered Cone Trim - Black Alzak® Cone, White Trim Ring 6" Adjustable Tapered Cone Trim - Haze Cone, White Trim Ring 6" Adjustable Tapered Cone Trim - Wheat Haze Cone, White Trim Ring	IC2/TC2/TC2R: 75W PAR30 IC22/IC22 W/IC22 S/IC22R: 50W PAR30 IC23/IC23 W: 50W PAR30 APT2: 75W PAR30

Housing and trim can be ordered together or separate, but will always ship separately.