



Trac-Master™ Designer Exclusives

A contemporary fixture collection for a range of applications

JUNO®



Designer Exclusives

Juno Designer Exclusives present a contemporary-yet-timeless appearance that is ideal for a broad range of commercial and residential applications, including task, accent and vertical surface lighting; as well as display,

exhibition and gallery lighting. This striking fixture collection provides effective, illumination and makes a bold statement no matter what the environment, no matter what the décor.



T640 with T537 Transformer

T645

Gyrus™

A new spin on a traditional design, the Gyrus combines dramatic aerodynamic styling with the convenience of a front relamping gimbal ring. The MR16 has an integral accessory holder that accepts up to two standard 2" diameter lenses and louvers. An optional snap-in, dual accessory holder is available for the PAR30 that smartly integrates into the die cast aluminum fixture design.

Finishes

White (WH) Black (BL) Silver (SL)

Series	Lamp	Dimensions
T640	12V, 20-50W MR16CG	

With integral Dual Accessory Holder

See specification sheet for optional accessories.

T537 and T538 Transformer required. Must be ordered separately.

Finishes: WH, BL, SL

Series	Lamp	Dimensions
T645	35-75W PAR30	

See specification sheet for optional accessories.

Finishes: WH, BL, SL

20-75VA 12V Transformers

Both T537 and T538 are available in white, black or silver finishes.

T537	
T538	



Aerodynamic Perfection

Reminiscent of precision aerodynamics, the Gyrus™ adds a touch of technical elegance to your environment. With the convenience of front relamping and the versatility of dual-accessory capability, Gyrus represents the perfect marriage of functionality and style.