

Canopies & Pendant Stems



Large Canopies

Used in conjunction with pendant stems for electrical feed and mechanical support of track. 4 3/4" diameter.

Canopy for T-Bar Ceilings

Mounts onto T-bar runner and can be fed via flexible metal conduit or non-metallic cable entering into the top of the ceiling mounting plate. **TF90 SL**

Canopy for Rigid Ceilings

Mounts over standard ceiling outlet boxes. **TF91 SL**



Mini-Canopies

Used in conjunction with pendant stems or 10-24 threaded rod (not supplied) for mechanical support of trac. Secures to ceiling with toggle bolt (supplied), wood screw or optional T-bar attachment clip. 2 1/4" diameter. Versions include:

- TF92 SL** Mini-Canopy for Pendant Stems
- TF93 SL** Mini-Canopy for 10-24 Threaded Rod
- R37F** T-bar Attachment Clip*
- R37D** T-bar Attachment Clip with Space for Ceilings Using Dropped Tiles*

*T-Bar clips must be ordered separately.



Sloped Ceiling Adapter

Permits pendant stems to be hung vertically from sloped ceilings. Used in conjunction with Rigid Ceiling or Pendant Stem Ceiling Canopies (not included). Allows feeding of wires to track at up to a 60 degree angle. Accommodates a maximum of two 12 gauge solid THHN copper wires. 20-amp capacity. **T94 SL**




Pendant Stems

Threaded top and bottom permit attachment at the top to canopy assemblies, and at the bottom to electrical feed/support cylinders. Inside diameter accommodates two 10 gauge solid THHN copper wires.

- TFPS 3IN SL** 3 1/2" Stem
- TFPS 12IN SL** 12" Stem
- TFPS 18IN SL** 18" Stem
- TFPS 24IN SL** 24" Stem
- TFPS 36IN SL** 36" Stem
- TFPS 48IN SL** 48" Stem

T96 SL Pendant Stem Coupling



Wall/Feed Mechanical Support

Flex 12™ may be mechanically supported perpendicular to the wall and electrically fed through a wall-mounted outlet box that is wired to the transformer secondary.

Specify:
(1) TF45 SL

Wall/Feed Mechanical Support

Flex 12™ may be mounted parallel to the wall and electrically fed when installed over a wall-mounted outlet box that is wired to the transformer secondary.

Specify:
(1) TF530 SL or (1) TF529 SL

Wall Mount Electrical Feeds & Mechanical Supports



Wall Feed/Support Canopy

Electrically feeds and/or mechanically supports the trac perpendicular to wall. Mounts directly to wall or over standard 4" outlet boxes. 25-amp capacity. 5" diameter. **TF45 SL**



Outrigger Electrical Feed and Mechanical Support

Used to mechanically support and electrically feed power to the track in a parallel to wall installation. Extends 5 1/2" from wall. One electrical feed outrigger per circuit is required.

Electrical Feed Outrigger

25-amp capacity. Mounts over standard 4" wall outlet boxes. 5" diameter. **TF529 SL**

Mechanical Support Outrigger

Canopy fastens to wall with toggle bolts (supplied) or wood screws. 3" diameter. **TF530 SL**