

Outdoor General Purpose Lighting

Philips Keene outdoor luminaires are your best value because they are innovative, contractor friendly, and energy efficient. Readily available and dependable, Keene solutions cover a wide variety of applications for your day to day outdoor lighting needs.



Performance is key.

Philips Keene is committed to offering solutions that are tailored to meet your lighting needs. We have developed a classification system to help you choose the right product every time.

Star Rating System

Good	*
Better	**
Best	***

Outdoor General Purpose Lighting

Catalogue no.	Rating	Lamp	Watts	Ballast/Voltage	Service Quantity		Appl. Page	
					2 days	10 days		
Wall Mount								
WPS Wallprism								
WPS070NLXL-1	*	ED17 HPS	70	Reactor (NPF)/120V	40		109	
TLW Wallprism								
TLW050NLXLPC-1	*	E17 HPS	50	Reactor (NPF)/120V	15		109	
TLW070NLXLPC-1	*	E17 HPS	70	Reactor (NPF)/120V	100		109	
TLW070NLXLPC-1W	*	E17 HPS	70	Reactor (NPF)/120V	30			
Mini & Maxi								
313150LXL-T	**	ED17 HPS	150	HX-HPF /Tri-Tap	50		109	
313150NLXL-1	**	ED17 HPS	150	Reactor (NPF)/120V	100		109	
313175MAL-T	**	ED17 MH	175	CWA/Tri-Tap	100		109	
553250LXL-T	**	E18 HPS	250	CWA/Tri-Tap		20	109	
553250MAL-T	**	ED28 MH	250	CWA/Tri-Tap	40		109	
553400LXL-T	**	E18 HPS	400	CWA/Tri-Tap		15	109	
553400MAL-T	**	ED37/BT37 MH	400	CWA/Tri-Tap	40		109	
Mini & Maxi Accessories								
330		Wire Guard for 300 Series Wallcube					15	
335		Lexan Shield for 300 Series Wallcube					15	
LytePro7								
LP7T	***	555 Lumen LED	13	120-220	50			
LP7P	***	555 Lumen LED	13	120-220	50			
LytePro16								
LP16T	***	2500 Lumen LED	36.5	120-277	30			
LP16P	***	2500 Lumen LED	36.5	120-277	30			
LytePro32								
LP32T	***	5700 Lumen LED	71	120-277	20			
LP32T-H	***	5700 Lumen LED	71	347-480	20			
LP32P	***	5700 Lumen LED	71	120-277	20			
LP32P-H	***	5700 Lumen LED	71	347-480	20			

NOTE: "T" - Titanium finish, "P" - Bronze finish

