


Specular Alzak® Cone ☆☆



1105TCL Specular Clear Alzak®
1105TCD Clear Diffuse

2 x 13W QT		
Ht. to Floor	F.C.	Beam Dia.
	At 30° Above Floor	
8'	15	14'
9'	11	16'
10'	8	18'
Multiple Units		
Ctr. to Ctr.	Footcandles	
	Lrg. Room	Sml. Room
4'	57	42
5'	40	28
6'	27	14




Specular clear Alzak® aperture cone and Quad Tube lamps provide best efficiency. High reflectivity white reflector for maximum reflectance.

Frame-In Kit	Ceiling	Wattage	Lamping
1101T13U 1101T13-347	Non-IC	13W	(2) Quad
1101T18U 1101T18-347	Non-IC	18W	(2) Quad
1101T26U 1101T26-347	Non-IC	26W	(2) Quad
CS1102T26UWH CS1102T26-347WH CS1102T26UBK CS1102T26-347BK	Surface	26W	(2) Quad

1105TCL

Premium Die-Cast Step Baffle ☆☆



1105TBK Black Baffle
1105TWB White Baffle

2 x 13W QT		
Ht. to Floor	F.C.	Beam Dia.
	At 30° Above Floor	
8'	12	14'
9'	8	16'
10'	6	18'
Multiple Units		
Ctr. to Ctr.	Footcandles	
	Lrg. Room	Sml. Room
4'	35	26
5'	25	17
6'	17	9




Versatile low brightness downlight with precision-fitted die-cast aluminum step baffle and high reflectivity white reflector. Recommended for use with 26W QT lamps.

Frame-In Kit	Ceiling	Wattage	Lamping
1101T13U 1101T13-347	Non-IC	13W	(2) Quad
1101T18U 1101T18-347	Non-IC	18W	(2) Quad
1101T26U 1101T26-347	Non-IC	26W	(2) Quad
CS1102T26UWH CS1102T26-347WH CS1102T26UBK CS1102T26-347BK	Surface	26W	(2) Quad

1105TBK

Cross Blade ☆☆☆



1132TA Satin Aluminum Louver
1132TWB White Louver

2 x 13W QT		
Ht. to Floor	F.C.	Beam Dia.
	At 30° Above Floor	
8'	14	11'
9'	10	12.5'
10'	8	14'
Multiple Units		
Ctr. to Ctr.	Footcandles	
	Lrg. Room	Sml. Room
4'	39	28
5'	28	19
6'	18	9



Exclusive cross blade louver provides a well-shielded soft lighting effect. High reflectivity white reflector. Ideal for corridor lighting, it offers a very wide lighting distribution with optimum glare control.

Frame-In Kit	Ceiling	Wattage	Lamping
1101T13U 1101T13-347	Non-IC	13W	(2) Quad
1101T18U 1101T18-347	Non-IC	18W	(2) Quad
1101T26U 1101T26-347	Non-IC	26W	(2) Quad
CS1102T26UWH CS1102T26-347WH CS1102T26UBK CS1102T26-347BK	Surface	26W	(2) Quad

1132TWB

Note: For dimming options, please consult the corresponding product Spec Sheet on www.canlyte.com.