



# Lytepoints Low Voltage 3 3/4"

## Cone Adj. MR16 3 3/4 Brushed Steel

Cone Adj. MR16 3 3/4 Brushed Steel

LytePoints low-voltage and line-voltage luminaries represent the ultimate in small aperture downlighting. They are designed to deliver superior performance, maximum versatility and fast, easy installation. A diverse selection of trims and finishes combined with universal frame-in kits, with magnetic or electronic transformers, offer the perfect lighting solution for virtually every application. From fully adjustable accent lights to wet location and decorative luminaries, LytePoints provides the tools to help you realize the full potential of your design.

### Product data

General Information		Shape	Round
Lamp Watts	37/50		
Lamp Envelope Code	MR-16		
Number of Lamps	1		
Downlight Type	Accent Adjustable		
Mounting	Recessed franse vertaling		
Operating and Electrical		Product Data	
Maximum Lamp Watts	50	Order product name	Cone Adj. MR16 3 3/4 Brushed Steel
		Commercial Code	304STPX
		Order code	304STPX
		Catalog Number Description	Cone Adj. MR16 3 3/4 Brushed Steel
		Service / Spec Smart	-
		Material Nr. (12NC)	LIGC00004147
Mechanical and Housing			
Aperture Size Code	3 3/4 in		