

PHILIPS LIGHTOLIER

Downlighting

LyteProfile

6" Round downlight
and Lensed wall wash



Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____

LyteProfile LED Downlights are designed for new construction and include downlight and wall wash distributions. They are highly energy efficient with up to 100lm/W, provide a full 60° cutoff, and feature an impressively, shallow 4.5" housing.

Complete Product = Frame-in kit + Light engine + Reflector Order each separately

Ordering guide: Frame-in kit¹

Example: P6RD15NZ10UVBEM

Series	Style	Lumens	Installation	Dimming	Input voltage	Version	Options
P6R	D		N			VB	
P6R LyteProfile 6" Round	D Downlight	10 1,000 lm	N Non-IC New construction	Z10 0-10V Dimming L Lutron	U Universal (120/277v) 3 347V ²	VB Version B	EM Emergency ² LC Chicago plenum
		15 1,500 lm					
		20 2,000 lm					
		25 2,500 lm	N Non-IC New construction	Z10 0-10V Dimming L Lutron	1 120V 2 277V 3 347V ²		

Ordering guide: Light engine

Example: P6RD835VB

Series	Style	CRI	CCT	Version	Options
P6R	D	8		VB	
P6R LyteProfile 6" Round	D Downlight	8 80	27 2700K 30 3000K 35 3500K 40 4000K	VB Version B	LC Chicago plenum

For 90 CRI, contact factory.

Ordering guide: Reflector

Example: P6RDCCP

Series	Style	Reflector	Flange
P6R			
P6R LyteProfile 6" Round	D Downlight LW Lensed wall wash	CL Clear	Blank White (painted)
		CC Comfort clear	P Polished (matches aperture)
		D Clear diffuse (applied)	
		W White (painted)	Blank White (painted)

1. Mounting Bars need to be ordered separately, see Options and Accessories on page 2 for Mounting Bar options.

2. 347V configurations are not available with the emergency option.

Note: Refer to page 2 for Energy Star certification details.

Note: Chicago Plenum (LC) is not available with 347V.

