



# PAR30/PAR20 LED

## 10PAR30L/LED/830/F40/DIM/ULW/120V 6/1FB

Philips PAR30 and PAR20 LED Single Optic Lamps provide superior lighting aesthetics and optimal thermal efficiency in a sleek, lightweight design.

### Product data

General Information	
Cap-Base	E26 [ Single Contact Medium Screw]
Nominal Lifetime (Nom)	25000 h
Switching Cycle	25000X
Technical Type	10-75W
Light Technical	
Color Code	830 [ CCT of 3000K]
Beam Angle (Nom)	40 °
Initial lumen (Nom)	850 lm
Luminous Flux (Rated) (Nom)	850 lm
Luminous Intensity (Nom)	1600 cd
Color Designation	White (WH)
Rated Beam Angle	40 °
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	85.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	10 W
Lamp Current (Nom)	86 mA
Wattage Equivalent	75 W


Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	67 °C
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Suitable For Accent Lighting	Yes
Product Data	
Order product name	10PAR30L/LED/830/F40/DIM/ULW/120V 6/1FB
EAN/UPC - Product	046677529741
Order code	529743
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929001322104
Net Weight (Piece)	0.285 kg

# PAR30/PAR20 LED

## Warnings and Safety

- Suitable for use in damp locations.
- Not for use in totally enclosed luminaires.
- Before replacing, turn off power and let lamp cool to avoid electrical shock or burn.
- CAUTION: Risk of electric shock— do not use where directly exposed to water
- NOTES: This device complies with Part 18 of the FCC rule. This product may cause interference with other devices. If interference occurs, change the location of the products involved. This RFLD device complies with Canadian ICES-005.


## Dimensional drawing




PAR30L 120V 9-75W 850lm 40D 3000K E26 D

Product	D	C
10PAR30L/LED/830/F40/DIM/ULW/120V 6/1FB	94 mm	118 mm


## Photometric data



10-75W E26 PAR30L 40D 830 3000K




10-75W E26 PAR30L



10-75W E26 PAR30L 40D 830 3000K

# PAR30/PAR20 LED

## Lifetime



14-120W E26 PAR38

14-120W E26 PAR38

