

HALOGEN LAMPS

Ecovantage, Halogená Lamps

Watts	Bulb	Base	Product Number	Symbols, Footnotes	Ordering Code	Volts	Pkg. Qty.‡	Description	Class, Filament	MOL (In.)	Rated Avg. Life (Hrs.)(93)	Approx. MBCP*	Lumens
29	A19	Med.	40983-9	\$@□†(103)	29A19/EV	120	12	White	C, CC-8	4 $\frac{1}{16}$	1000	—	380
			41050-6	\$@□†(103)	29A19/EV/CL	120	12	Clear	C, CC-8	4 $\frac{1}{16}$	1000	—	380
43	A19	Med.	40948-7	\$@□†(103)	43A19/EV	120	12	White	C, CC-8	4 $\frac{1}{16}$	1000	—	750
			41049-8	\$@□†(103)	43A19/EV/CL	120	12	Clear	C, CC-8	4 $\frac{1}{16}$	1000	—	750
			22695-1	\$@□†(103)	43A19/EV/NTL	120	12	Natural Light	C, CC-8	4 $\frac{1}{16}$	1250	—	630
53	A19	Med.	22696-9	\$@□†(103)	53A19/EV/NTL	120	12	Natural Light	C, CC-8	4 $\frac{1}{16}$	1250	—	830
72	A19	Med.	40982-1	\$@□†(103)	72A19/EV	120	12	White	C, CC-8	4 $\frac{1}{16}$	1000	—	1490
			41048-0	\$@□†(103)	72A19/EV/CL	120	12	Clear	C, CC-8	4 $\frac{1}{16}$	1000	—	1490
			22699-3	\$@□†(103)	72A19/EV/NTL	120	12	Natural Light	C, CC-8	4 $\frac{1}{16}$	1000	—	1200

HALOGENÁ ENERGY SAVER

40	T60	Med.	20967-6	\$@□(103)	40T60/HES/WH	120	6	White	C, CC-8	4 $\frac{1}{8}$	3000	—	800
	R20	Med.	21202-7	\$@□(104)	40R20/HES/FL	120	6	Flood	C, CC-8	3 $\frac{1}{16}$	3000	—	570
	BR30	Med.	20970-0	\$@□(104)	40BR30/HES/FL	120	5	Flood	C, CC-8	5 $\frac{1}{8}$	3000	—	600
	BR40	Med.	20972-6	\$@□(104)	40BR40/HES/FL	120	4	Flood	C, CC-8	6 $\frac{1}{2}$	3000	—	630
50	BR30	Med.	22998-9	\$@□(104)	50BR30/HES/FL	120	5	Flood	C, CC-8	5 $\frac{1}{8}$	3000	—	800
70	BR40	Med.	22999-7	\$@□(104)	70BR40/HES/FL	120	4	Flood	C, CC-8	6 $\frac{1}{2}$	3000	—	1285
	T60	Med.	20969-2	\$@□(103)	70T60/HES/WH	120	6	White	C, CC-8	4 $\frac{1}{8}$	3000	—	1600

HALOGENÁ ENERGY ADVANTAGE PRO PACKS (102)

40	T60	Med.	21354-6	\$@□†(103)	40T60/HEA/WH	120	12	White	C, CC-8	4 $\frac{1}{8}$	3000	—	800
	R20	Med.	22236-4	\$@□†(104)	40R20/HEA/FL	120	12	Flood	C, CC-8	3 $\frac{1}{16}$	3000	450	—
	BR30	Med.	21359-5	\$@□†(104)	40BR30/HEA/FL	120	12	Flood	C, CC-8	5 $\frac{1}{8}$	3000	2250	—
	BR40	Med.	22238-0	\$@□(104)	40BR40/HEA/FL	120	12	Flood	C, CC-8	6 $\frac{1}{2}$	3000	—	630
50	T60	Med.	21356-1	\$@□†(103)	50T60/HEA/WH	120	12	White	C, CC-8	4 $\frac{1}{8}$	3000	—	1100
	BR30	Med.	22994-8	\$@□†(104)	50BR30/HEA/FL	120	12	Flood	C, CC-8	5 $\frac{1}{8}$	3000	—	800
70	BR40	Med.	22997-1	\$@□†(104)	70BR40/HEA/FL	120	12	Flood	C, CC-8	6 $\frac{1}{2}$	3000	—	1285
	T60	Med.	21358-7	\$@□(103)	70T60/HEA/WH	120	12	White	C, CC-8	4 $\frac{1}{8}$	3000	—	1600

HALOGENÁ CLASSIC BLISTER-CARDED (96)

60	BT15	Med.	24924-3		BC60BT15/HAL/CL	120	10	Clear, Blister Card	C, CC-8	4	3000	—	900
			24926-8		BC60BT15/HAL/W	120	10	White, Blister Card	C, CC-8	4	3000	—	840
			38915-5		BC60BT15/HAL/W	120	80	White, Blister Card	C, CC-8	4	3000	—	840
75	BT15	Med.	24927-6		BC75BT15/HAL/W	120	10	White, Blister Card	C, CC-8	4	3000	—	1120
100	BT15	Med.	24931-8		BC100BT15/HAL/W	120	10	White, Blister Card	C, CC-8	4	3000	—	1670
150	BT15	Med.	24933-4		BC150BT15/HAL/W	120	10	White, Blister Card	C, CC-8	4	3000	—	2650

For the most current product information, go to the e-catalog on www.philips.com

Halogen symbols and footnotes located on page 116

