

Fish Tape Selection Guide



Length	Width & Thickness	Case Diameter	End Type	Tuff-Grip™ Pro	Rapid-Pak®	Thumb-Winder™	Replacement Tapes
Blued Steel							
25	1/8 in. x .045 in.	7 in.	Formed hook	–	–	31-012	–
50	1/8 in. x .045 in.	7 in.	Formed hook	–	–	31-010	–
50	1/8 in. x .060 in.	9 in.	Formed hook	31-033**	–	–	–
60	1/8 in. x .060 in.	12 in.	Formed hook	31-055	–	–	31-035
100	1/8 in. x .060 in.	12 in.	Formed hook	–	31-081†	–	31-036
120	1/8 in. x .060 in.	12 in.	Formed hook	31-056	–	–	31-036
200	1/8 in. x .060 in.	12 in.	Formed hook	–	31-098†	–	31-038
240	1/8 in. x .060 in.	12 in.	Formed hook	31-057	–	–	31-038
500	1/8 in. x .060 in.	None	Formed hook	–	–	–	31-3380
700	1/8 in. x .060 in.	None	Formed hook	–	–	–	31-3379
50	1/4 in. x .060 in.	12 in.	Formed hook	31-058	–	–	31-051
100	1/4 in. x .060 in.	12 in.	Formed hook	31-059	–	–	31-050
200	1/4 in. x .060 in.	12 in.	Formed hook	–	–	–	31-052
300	1/4 in. x .060 in.	None	Formed hook	–	–	–	31-2127
400	1/4 in. x .060 in.	None	Formed hook	–	–	–	31-2128
600	1/4 in. x .060 in.	None	Formed hook	–	–	–	31-2980
750	1/4 in. x .060 in.	None	Formed hook	–	–	–	31-2139
1,000	1/4 in. x .060 in.	None	Formed hook	–	–	–	31-3384
10,000	1/4 in. x .060 in.	None	Formed hook	–	–	–	31-2982
Stainless Steel							
120	1/8 in. x .060 in.	12 in.	Formed hook	31-066	–	–	31-073
240	1/8 in. x .060 in.	12 in.	Formed hook	31-067	–	–	31-074
S-Class® Nylon Jacketed Fiberglass							
50	3/16 in. diameter	12 in.	Leader	31-060	31-187†	–	31-150
50	3/16 in. diameter	12 in.	Eyelet	31-062	31-190†	–	31-160
100	3/16 in. diameter	12 in.	Leader	31-061	31-186†	–	31-152
100	3/16 in. diameter	12 in.	Eyelet	31-063	31-189†	–	31-162
200	3/16 in. diameter	16 in.	Leader	31-064*	31-207†	–	31-155
200	3/16 in. diameter	16 in.	Eyelet	31-065*	31-208†	–	31-165
300	3/16 in. diameter	None	Eyelet	–	–	–	31-2138
400	3/16 in. diameter	None	Eyelet	–	–	–	31-400
500	3/16 in. diameter	None	Eyelet	–	–	–	31-3370
Gold-Fish® Brass Plated Steel Coil							
25	3/16 in. diameter	None	Eyelet	–	–	–	31-140
50	3/16 in. diameter	12 in.	Eyelet	31-144	–	–	31-141
100	3/16 in. diameter	None	Eyelet	–	–	–	31-142
Zoom™ Nylon Jacketed Stainless Steel							
50	3/16 in. diameter	12 in.	Eyelet	31-090	–	–	31-091
100	3/16 in. diameter	12 in.	Eyelet	31-092	–	–	31-093
200	3/16 in. diameter	16 in.	Eyelet	31-096*	–	–	31-097

*16 in. diameter Tuff-Grip™ Case †16 in. diameter Rapid-Pak® Case

**9 in. diameter Tuff-Grip™ Pro Case

Description	Cat. No.
Fish Tape Leader for steel or stainless steel tapes	31-148
Fish Tape Leader for S-Class® Fiberglass	31-159
Multi-Wire Pulling Leader – 6-loop	31-146
Multi-Wire Pulling Leader – 4-loop	31-147

Description	Cat. No.
Fish Tape Swivel Ball	31-085
Replacement Eyelets (4) for S-Class®	31-158
Replacement Eyelets (2) for Zoom™	31-094

Tuff-Grip™ Pro Fish Tapes

- Tuff-Cuff™ tape retaining feature keeps tape properly positioned in the opening
- Full-perimeter handle band helps keep dirt and moisture out, prolonging life
- Easier to install replacement tapes
- Superior pull-out and rewind characteristics
- Exceptionally durable case and handle
- Clean contemporary styling
- Large, comfortable ergonomically-designed handle, grasp from the top or side. Allows for use with gloves.



Width & Thickness	End Type	Cat. No.	Replacement Tape Cat. No.
Blued Steel			
1/8" x .060" x 60'	Formed Hook	31-055	31-035
1/8" x .060" x 120'	Formed Hook	31-056	31-036
1/8" x .060" x 240'	Swivel Ball End	31-225	31-038 & 31-085
1/8" x .060" x 240'	Formed Hook	31-057	31-038
Stainless Steel			
1/8" x .060" x 120'	Formed Hook	31-066	31-073
1/8" x .060" x 240'	Formed Hook	31-067	31-074
S-Class® Nylon Jacketed Fiberglass			
3/16" diameter x 50'	Leader	31-060	31-150
3/16" diameter x 50'	Eyelet	31-062	31-160
3/16" diameter x 100'	Leader	31-061	31-152
3/16" diameter x 100'	Eyelet	31-063	31-162
Nylon Monofilamet			
3/16" diameter x 50'	Eyelet	31-542	31-552
3/16" diameter x 100'	Eyelet	31-544	31-554
Gold-Fish® Brass Plated Steel Coil			
3/16" diameter x 50'	Eyelet	31-144	31-141
Zoom™ Nylon Jacketed Stainless Steel			
3/16" diameter x 50'	Eyelet	31-090	31-091
13/16" diameter x 100'	Eyelet	31-092	31-093