

Detectable Underground Tapes

- Solid aluminum foil core tapes for protection, location and identification of underground utility installations
- Meets or exceeds industry standards including the American Public Works Association (APWA) color code
- Formulated to resist degradation from acid and alkali found in soils
- Lead-free pigments and organic lead-free ink

Property	Method	Value
Thickness	ASTMD2103	5.0 Mils
Elongation	ASTMD882-75B	80%
Composition	IDEAL Specs.	Bottom layer PE Top layer PET Foil industry standard
Tensile Strength	ASTMD882	35 lbs./in. (15,000 PSI)

Legend	Color	Size	Cat. No.	
Caution Buried Electric Line Below	Red	3 in. x 1,000 ft.	42-201	
Caution Buried Electric Line Below	Red	6 in. x 1,000 ft.	42-251	
Caution Buried Fiber Optic Line Below	Orange	6 in. x 1,000 ft.	42-252	

Non-Detectable Underground Tapes

- For protection, location and identification of underground utility installations
- Formulated to resist degradation from acid and alkali found in soils
- Lead-free pigments and organic lead-free ink

Property	Method	Value	
Thickness	ASTMD2103	4.0 Mils	
Elongation	ASTMD882-75B	500%	
Composition	IDEAL Specs.	LDPE	
Tensile Strength	ASTMD882	2,750 PSI	

Recommended Burial Depth

3 in. Tape - 4 in. to 6 in.

6 in. Tape – less than 12 in.

0 III. 1apt - 1633 tilati 12 III.				
Legend	Color	Size	Cat. No.	
Caution Buried Electric Line Below	Red	3 in. x 1,000 ft.	42-101	
Caution Buried Electric Line Below	Red	3 in. x 250 ft.	42-131	
Caution Buried Electric Line Below	Yellow	3 in. x 1,000 ft.	42-102	
Caution Buried Telephone Line Below	Orange	3 in. x 1,000 ft.	42-103	
Caution Buried Fiber Optic Line Below	Orange	3 in. x 1,000 ft.	42-104	
Caution Buried Electric Line Below	Red	6 in. x 1,000 ft.	42-151	
Caution Buried Electric Line Below	Yellow	6 in. x 1,000 ft.	42-152	

Barricade Tapes



- High-visibility safety yellow or red polyethylene construction with bold black letters
- Meets OSHA specifications Section 1010.144 for marking physical hazards

Property	Method	Value
Elongation	ASTM D88-75B	≥ 400%
Composition	IDEAL Specs.	LDPE
Tensile Strength	ASTM D882	2,350 PSI TD 1,893 PSI MD

Legend	Color	Size	Thickness	Cat. No.
Caution	Yellow	3 in. x 1,000 ft.	4.0 Mils	42-001
Caution Do Not Enter	Yellow	3 in. x 1,000 ft.	4.0 Mils	42-002
Caution High Voltage	Yellow	3 in. x 1,000 ft.	4.0 Mils	42-003
Danger	Red	3 in. x 1,000 ft.	4.0 Mils	42-051
Danger High Voltage 277V/480V Keep Out	Red	3 in. x 1,000 ft.	4.0 Mils	42-052

Legend	Color	Size	Thickness	Cat. No.
Caution	Yellow	3 in. x 250 ft.	2.0 Mils	42-031
Caution	Yellow	3 in. x 1,000 ft.	2.0 Mils	42-011
Caution Do Not Enter	Yellow	3 in. x 1,000 ft.	2.0 Mils	42-012
Danger	Red	3 in. x 1,000 ft.	2.0 Mils	42-015