

Coax/UTP Cable Stripper

- Features a primary and secondary strip cartridge
- Strips UTP, RG-59 and RG-6 coax cable
- Rotates easily around finger
- Push-on ring for easy connector termination

Description	
Coax/UTP Cable Stripper	



Coax Stripmaster® Wire Strippers

- Speeds 2-step cable stripping
- Spring-action operation grips and strips in one
- Knife-type blades feature multiple hole diameters sized for two step removal of outer jacket insulation and center conductor

Description	Coax Cable Type (RGU)	Repl. Blade Cat. No.	Cat. No.
Coax Stripmaster® for RG-6	RG-6	LB-740	45-262
Coax Stripmaster® for RG-59	RG-59	LB-743	45-265
Coax Stripmaster® for RG-6 Quad Shield	RG-6 Quad Shield	LA-3953	45-282

Coax Cable Stripper

- For RG-6, RG-6 Quad and RG-59
- No adjustment required
- Strips center conductor and cable jacket

	Description		Cat. No.
	Coax Cable Stripper		45-320
	Coax Connector Kit w/four Push-On F-Co	nnectors	33-320

Toggle® Coax Strippers

Toggle® Tools for stripping Ethernet, Thinnet, RG-62 or RG-59 coax cable and other cable sizes

	8	
Description	0040	Cat. No.
Coax Stripper for RG-8/11U		45-510
Coax Stripper for RG-6		45-513

Coax Strippers

Specific adjustments needed for each cable size

Description	Replacement Cassette	Cat. No.
Coax Stripper - 3 Step • For crimp BNC and TNC conn. • Strips braid 0.240 in. or 6mm and Dielectric 0.240 in. or 6mm	45-522 (Black)	45-520
Coax Stripper - 3 Step • For dual crimp BNC/TNC and Thinnet BNC conn. • For 735A Belden® cable • Strips braid 0.328 in. or 8.2mm and dielectric 0.109 in. or 2.7mm	45-523 (Brown)	45-521
Coax Stripper - 2 Step • For F-Type, many single crimp BNC/TNC's, Twist-on BNC/TNC's, Twinax and UHF conn. • Strips 0.250 in. or 6.35mm	45-524 (Blue)	45-526

UTP Cable Stripper

- Strips Cat 3, 5, 5e & 6 cables
- One step stripping

Description	Cat. No.
UTP Cable Stripper	45-167

Cyclops® Data Cable Stripper

Fast, easy removal of outer sheath insulations (PVC and Plenum types, UTP & STP)

Description		Cat. No.
Data Cable Stripper for unshielded and shielded	twisted pair cable	45-514

UTP/STP/Coaxial Cable Strippers

Adjustable blades can be set for any depth to help ensure nick-free strips



Description	Typical RG Cables	Cat. No.
Coaxial Cable Stripper, up to 1/8 in. (3.2mm) O.D	RG-174, RG-187	45-162 (Gray)
Coaxial Cable Stripper, 1/8 in. (3.2mm) to 7/32 in. (5.556mm) O.D.	RG-58,CB Antenna Cable	45-163 (Blue)
Coaxial Cable Stripper, 1/4 in. (6.4mm) to 9/16 in. (14.3mm) O.D.	RG-11, RG-8	45-164 (Blue)
Cable Stripper, 3/16 in. (4.8mm) to 5/16 in. (8mm) O.D.	RG-59, UTP Cable	45-165 (Black)
Replacement Blade Set* for 45-162, 45-163, 45-165	_	L-9225
Replacement Blade Set* for 45-164	_	L-9226

^{*}A set of blades consists of three straight blades and one round blade.

DataComm Equipment

Digital Cable Splitter

- Nickel-plated housing
- High-performance impedancebalanced Printed Circuit Board design
- Bandwidth: 5MHz 1 GHz Impedance: 75 Ohm
- Over 120 dB of RFI shielding
- Low insertion loss
- Splits signals up to 8 outlets
- Terminators (85-038) needed for all unused ports for optimal performance

Description	Cat. No.
Digital Cable Splitter, 8-Way	85-138

Diplexer, 2.3 GHz

- Combine or split cable/ antenna signals with satellite signals
- High quality PCB design
- Corrosion-resistant sealed construction
- Nickel-plated die-cast zinc housing
- High-quality machined threads for quick connections
- Grounding hole for up to 6 AWG wire

Description	Cat. No.
Diplexer, 2.3 GHz, SATV/TV Combiner Splitter	85-323

Grounding Block

- Solid zinc alloy, nickel plated and chromate finished
- High performance 360° beryllium copper contact
- Excellent electrical performance 0 - 3,000 MHz
- Dual grounding holes can accept up to #6 wire
- UL/CSA approved

Description	Cat. No.
2-Port Grounding Block for F-Connectors	85-311

Mini Coax Stripper

 Adjustable stripper for mini coax cable



Description	Cat. No.
Mini Coax Stripper	45-529

Coax Connector Tool - F & BNC

- Works on compression and hex connectors
- Makes attaching (and detaching) connector to equipment easier
- Aids in installing CATV connectors on coax cable
- New comfort grip handle



Description	Cat. No.
Coax Connector Tool - F & BNC	35-046

4-Way Indent Crimp Tools

Crimp solid barrel contacts for RS232 interface connectors. Feature four-way indent dies (per MS22520 specifications), full cycle ratchet, built-in pin and

socket locator and comfort-grip handles.

■ High-grade steel construction for outstanding performance

Description	Cat. No.
20-26 AWG (.519 mm²128 mm²) RS232 D-sub Round Barrel Contacts, Pins or Sockets	35-465
16-22 AWG (1.31 mm²324 mm²) Round Barrel Contacts, Pins,Sockets and Deutsch 16 Pin Contacts	35-466
Trompeter BNC Connector Center Pins	35-468

Economy Data and CATV Kit



Kit 33-915 Includes:

Kit oo 510 iiididada.		/
Description	Qty.	Cat. No.
Data T®-Cutter	1	45-074
Economy Coax Stripper	1	45-320
Economy UTP Stripper	1	45-167
Non-Impact Turn-Lock™ Tool w/110 Blade	1	35-492
Telemaster™ Telephone Tool	1	30-496
Economy Compression Tool	1	30-633
Mechanics Bag	1	35-535