

## Cables



85-770



85-780

- Customizable bulk cable
- Bulk CAT 5e solid 4-pair, CMR rated, 24 AWG, 350 MHz cable
- Bulk 2-conductor in-wall, 16 AWG speaker wire

Description	Cat. No.
CAT 5e Cable - 100 ft.	<b>85-780</b>
In-wall Speaker Wire - 50 ft.	<b>85-770</b>

## Insulation Displacement Connectors (IDC)



85-900

85-925

85-950



45-719

IDC connectors create fast splice and tap connections on solid copper wires. Designed for low voltage telecommunication cables.

- Moisture-resistant sealant protects wires from corrosion
- Use with solid copper single-conductor wire
- Kinetic Super™ Wire Stripper/Crimper easily cuts and strips 22 to 24 AWG solid wire

Description	Qty.	Cat. No.
UB-I, 2-Wire Tap Splice IDC	25	<b>85-900</b>
UR-I, 3-Wire Butt Splice IDC	25	<b>85-925</b>
UY-I, 2-Wire Butt Splice IDC	25	<b>85-950</b>
UR-I, 2-Wire Butt Splice IDC	100	<b>86-925</b>
UY-I, 2-Wire Butt Splice IDC	100	<b>86-950</b>
UB-I, 2-Wire Tap Splice IDC	1,000	<b>87-900</b>
UR-I, 3-Wire Butt Splice IDC	1,000	<b>87-925</b>
UY-I, 2-Wire Butt Splice IDC	1,000	<b>87-950</b>
IDC Combo Pack	25	<b>85-960</b>
Kinetic Super™ Wire Stripper/Crimper	1	<b>45-719</b>

## CAT 6 Modular Plugs

- Supports CAT 6
- Unique three-piece design provides easy installation and optimal performance
- Crimps with a standard RJ-45 crimp die
- 50 micron gold contacts, 8-position, 8-contact
- Suitable for solid or stranded conductors



Description	Qty.	Cat. No.
CAT 6 Modular Plugs	25	<b>85-366</b>

## TelCom Modular Plugs



85-403

85-396

85-394

- All plugs comply with FCC 68 guidelines and are UL Listed
- Plugs are capable of supporting the latest EIA/TIA cable system performance categories when installed in compliance with appropriate EIA/TIA standards and methods
- Plugs offered for round cable with solid conductors and for flat cable and stranded conductors
- Position and contact configurations cover popular styles

Description	Qty.	Cat. No.
6-Position 4-Contact Flat Stranded	25	<b>85-351</b>
	50	<b>85-401</b>
	100	<b>86-401</b>
6-Position 6-Contact Flat Stranded	25	<b>85-352</b>
	50	<b>85-402</b>
	100	<b>86-402</b>
4-Position 4-Contact Flat Stranded (Handset)	100	<b>86-398</b>
8-Position 8-Contact Flat Stranded	25	<b>85-353</b>
	50	<b>85-403</b>
6-Position 4-Contact Round Solid	100	<b>86-403</b>
	25	<b>85-344</b>
6-Position 6-Contact Round Solid	50	<b>85-394</b>
	100	<b>86-394</b>
6-Position 6-Contact Round Solid	100	<b>86-395</b>
8-Position 8-Contact CAT 6 Modular Plug	25	<b>85-366</b>
8-Position 8-Contact Round Solid	25	<b>85-346</b>
	50	<b>85-396</b>
	100	<b>86-396</b>