Tools and Totes

High-Speed Steel Flexible Bits, Type HS

Heavy duty split point high-speed steel drill bit

■ The best when encountering nailembedded wood, steel studs and steel plates

1	/	1	1
>	Bes ME	t for TAL	_<
Z	1	/	1

Best for MASONRY

Description	Shank	Cat. No.
3/8 in. x 24 in. High-speed Steel Flexible Bit	3/16	90-154
3/8 in. x 36 in. High-speed Steel Flexible Bit	3/16	90-155
3/8 in. x 54 in. High-speed Steel Flexible Bit	3/16	90-156
3/8 in. x 72 in. High-speed Steel Flexible Bit	3/16	90-157
1/2 in. x 24 in. High-speed Steel Flexible Bit	1/4	90-158
1/2 in. x 36 in. High-speed Steel Flexible Bit	1/4	90-159
1/2 in. x 54 in. High-speed Steel Flexible Bit	1/4	90-160
1/2 in. x 72 in. High-speed Steel Flexible Bit	1/4	90-161

Masonry Flexible Bits, Type M

- Masonry drill bit
- Designed for drilling in

lightweight masonly materials				
Description	Shank	Cat. No.		
3/8 in. x 54 in. Masonry Flexible Bit	3/16	90-124		
1/2 in x 72 in Masonry Flexible Rit	1/4	90-128		

Flexible Bit Extensions

- Three lengths available for 3/16 in. and 1/4 in. shaft diameters
- Connect to chuck end of shaft to increase the length of the bit



Description	Shank	Cat. No.
3/16 in. x 36 in. Flexible Bit Extension	3/16	90-170
3/16 in. x 54 in. Flexible Bit Extension	3/16	90-171
1/4 in. x 36 in. Flexible Bit Extension	1/4	90-173
1/4 in. x 54 in. Flexible Bit Extension	1/4	90-174

Flexible Bit Placement Tool

- Use as a positioning guide for the flexible drill bits
- Aids in more accurate placement of bit tips within walls
- Increases directional control during drilling

Description	Cat. No.
Flexible Bit Placement Tool	90-176

