



Main

Range of product	Homeline
Product or component type	Miniature circuit-breaker
Line Rated Current	30 A
System Voltage	120/240 V AC
Mounting mode	Plug-on
Poles description	2P
Short-circuit current	10 kA
Circuit breaker type	Standard
Circuit breaker application	HACR rated
Electrical connection	Screw clamp terminals

Complementary

Number of spaces required	2
AWG gauge	AWG 14...AWG 8 (aluminium/copper)

Environment

Product certifications	CSA
------------------------	-----

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1323 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations