



# CT230-GA/U

This power module with a built-in GFCI is controlled by a master thermostat to heat part of a large area



## MODEL & RATING

<b>CT230-240GA</b>	3600 W @ 240 V	15 A resistive	60 Hz	GFCI-5 mA
--------------------	----------------	----------------	-------	-----------

## SPECIFICATIONS

### SWITCHING ACTION

Epoxy-soundproofed relay: Quiet operation

### TEMPERATURE SETTING

Controlled by master thermostat

### DIMENSIONS (H•W•D)

124 x 70 x 23 mm / 4.9 x 2.8 x 0.9 inches

## FEATURES

**No setting dial** (settings controlled by master) means unit can be installed anywhere

**Ground Fault Circuit Interrupter (GFCI) included** - no need to buy separate safety cutoff

**GFCI test light** verifies safety cutoff is functioning properly and alerts if a leak is detected

**ON/STANBY switch** enables units' heating area to be shut down independently of other heating areas

**Linked units can operate on different voltages** (e.g., 5 units @ 120 V and 5 units @ 240 V)

**Can be installed locally or in utility rooms**

## ADDITIONAL INFORMATION

### Aube's Groud Fault Circuit Interrupter (GFCI)

- GA models meet UL and CSA standards for Class A GFCIs
- GA models cut power to the heating system when a 5 mA leak is detected; GB models cut power when a 30 mA leak is detected