BREAN



GLACIER SERIES



BCS3 MODEL

The smart choice

Air quality is a top concern for today's families. The Broan series, with its superior capture efficiency, is the ideal solution. What's more, this model's features provide the best quality and performance for the price.

CLEAN AND CONTEMPORARY

- · 2-speed performant blower, HVI* certified
- Quiet range hood offering a sound level of 1.5 sones at low speed
- Two high efficiency micro filters, easy to clean
- Two 50 W GU10 halogen bulbs (not included) provide warm and direct lighting
- Use charcoal filter HPF24 or HPF30 for a non-ducted installation

Captur

Provides faster smoke & odor removal



HIDDEN 2-SPEED ROCKER CONTROL



2-LEVEL HALOGEN LIGHTING (BULBS NOT INCLUDED)



TWO HIGH EFFICIENCY **MICRO FILTERS**

SPECIFICATIONS


WIDTH	MODEL	COLOR	VOLTS	AMPS	CFM	SONES (MIN./MAX.)	DUCTING
24"	BCS324SSC	STAINLESS STEEL	120	1.4	250	1.5/5.0	3 1/4" X 10" (H-V) 7" ROUND
24"	BCS324WWC	WHITE	120	1.4	250	1.5/5.0	3 1/4" X 10" (H-V) 7" ROUND
30"	BCS330SSC	STAINLESS STEEL	120	1.4	250	1.5/5.0	3 1/4" X 10" (H-V) 7" ROUND
30"	BCS330WWC	WHITE	120	1.4	250	1.5/5.0	3 1/4" X 10" (H-V) 7" ROUND
30"	BCS330BLC	BLACK	120	1.4	250	1.5/5.0	3 1/4" X 10" (H-V) 7" ROUND

ODTIONS

or none					
HPFAMM24	REPLACEMENT FILTERS FOR 24 IN MODEL				
HPFAMM30	REPLACEMENT FILTERS FOR 30 IN MODEL				
HPF24	CHARCOAL REPLACEMENT FILTERS FOR 24 IN MODEL				
HPF30	CHARCOAL REPLACEMENT FILTERS FOR 30 IN MODEL				







Broan-NuTone Canada ULC 1140 Tristar Drive Mississauga (Ontario) L5T 1H9 1-888-882-7626

www.broan.ca

87794B 01/17