

# WOBBLELIGHT

PORTABLE JOB-SITE LIGHTING

The **TOUGHEST**  
**WORKLIGHT** on  
the **PLANET!**

## Features and Benefits

- Lumen output from 8,000 – 40,000
- Lighting radius from 16 – 110 ft
- 36" Tall / 25 – 29 lbs
- Lexan dome w/ molded handle
- Tough reinforced ABS housing
- Floating bulb shock system
- Sealed on/off switch
- Fan-cooled lamp (400W and 500W)
- "No Burn" surface temperatures
- 110V power inlet & outlet
- 12 amp resettable circuit breaker
- Completely self-righting design



## Features and Benefits

- Lumen output 5,000
- Lighting radius 20 ft
- 27" Tall / 19 lbs
- Lexan PC dome w/ handle
- 85-watt spiral Fluorescent bulb
- Self-ballasted, instant-on technology
- Floating Shock System
- Integrated 5-foot power cord
- Low heat output, no hot surface
- Completely self-righting design



## Applications

- High-rise & building construction
- Commercial / residential construction
- Renovation / demolition / remediation
- Industrial maintenance & turn-arounds
- Tank and vessel inspection / repair
- Aircraft & ship building / maintenance
- Emergency / disaster response



Specifications / Model	WL85F	WL500H	WL175MH	WL400MH
Lamp Type	Fluorescent	Halogen	Metal Halide	Metal Halide
Watts	85	500	175	400
Lumen Output	5,000	8,000	15,000	40,000
Max. Lighting Range	20 ft.	24 ft.	42 ft.	110 ft.
Amps @ 110V	1.2	4.5	1.6	3.6
Lamp Life (Avg.)	5,000 hrs	2,000 hrs	15,000 hrs	15,000 hrs
Weight	18 lbs	24 lbs	26 lbs	29 lbs

ProBUILT Professional Lighting, LLC - 1170 Allanson Road, Mundelein, IL 60060

Toll Free: 877-707-0800 [www.probuiltlighting.com](http://www.probuiltlighting.com)