

# HANG-A-LIGHT®

## Hang-A-Light® Temporary Area Work Lights

Portable, bright and durable the Hang-A-Lights® are ceiling-mounted fixtures that give you 360° of light. These re-usable, temporary task lights have spring loaded clamps for easy installation and heavy metal cages with bottom guards for added safety.



HANG-A-LIGHT

### Hang-A-Light® 400 watt Pulse Start Metal Halide

- Modifiable for 120 / 208 / 240 / 277V
- Heavy-gauge steel construction
- NEC / OSHA compliant
- Suitable for damp location use
- 6-foot integrated power cord
- Lights 60 ft radius when mounted 15 ft above work area

### Hang-A-Light® 105 watt Fluorescent

- Energy Efficient 105 watt Fluorescent Bulb
- Self-Ballasted CFL Bulb, lightweight and flicker-free
- Electrical Receptacle, interconnect up to 8 units on 120V/15A service
- Energy Star Compliant light bulb
- 5-foot integrated power cord
- Suitable for damp locations



| HANG-A-LIGHT® UNIT                              | Mfr. Model No. | Lumens | Lamp Life   | Lighting Range |
|---|----------------|--------|-------------|----------------|
| Hang-A-Light® 400 watt Pulse Start Metal Halide | 111400PS       | 42,000 | 20,000 hrs. | 50 - 100 ft.   |
| Hang-A-Light® 105 watt Fluorescent              | 111105F        | 6,900  | 8,000 hrs.  | 20 - 30 ft.    |

For full list of available replacement parts see page 19