

NDR Electric

ENERGY STAR[®] : QUALIFIED PRODUCT LISTING

Product Number	Product Description
----------------	---------------------



RECESSED LIGHTING

RZR-400-9W-3K-WH	4" IC/NON-IC ULTRA THIN RECESSED LED, 9W, 3K, WHITE
RZR-400-9W-3K-SC	4" IC/NON-IC ULTRA THIN RECESSED LED, 9W, 3K, SATIN CHROME
RZR-400-9W-3K-BLK	4" IC/NON-IC ULTRA THIN RECESSED LED, 9W, 3K, BLACK
RZR-400-9W-4K-WH	4" IC/NON-IC ULTRA THIN RECESSED LED, 9W, 4K, WHITE
RZR-400-9W-4K-SC	4" IC/NON-IC ULTRA THIN RECESSED LED, 9W, 4K, SATIN CHROME
RZR-400-9W-4K-BLK	4" IC/NON-IC ULTRA THIN RECESSED LED, 9W, 4K, BLACK
RZR-600-12W-3K-WH	6" IC/NON-IC ULTRA THIN RECESSED LED, 12W, 3K, WHITE
RZR-600-12W-3K-SC	6" IC/NON-IC ULTRA THIN RECESSED LED, 12W, 3K, SATIN CHROME
RZR-600-12W-3K-BLK	6" IC/NON-IC ULTRA THIN RECESSED LED, 12W, 3K, BLACK
RZR-600-12W-4K-WH	6" IC/NON-IC ULTRA THIN RECESSED LED, 12W, 4K, WHITE
RZR-600-12W-4K-SC	6" IC/NON-IC ULTRA THIN RECESSED LED, 12W, 4K, SATIN CHROME
RZR-600-12W-4K-BLK	6" IC/NON-IC ULTRA THIN RECESSED LED, 12W, 4K, BLACK

LED BULB LISTING

A19

LED-A19-11W-27K	11W LED A19, 120V, 806LM, DIMMABLE, 2700K
LED-A19-11W-40K	11W LED A19, 120V, 806LM, DIMMABLE, 4000K

PAR20

LED-PAR20-7W-3K	7W LED PAR20, 120V, 525LM, DIMMABLE, 3000K
LED-PAR20-7W-4K	7W LED PAR20, 120V, 525LM, DIMMABLE, 4000K

PAR30

LED-PAR30LN-13W-3K	13W LED LONG NECK PAR30, 120V, 1000LM, DIMMABLE, 3000K
LED-PAR30LN-13W-4K	13W LED LONG NECK PAR30, 120V, 1000LM, DIMMABLE, 4000K

BR30

LED-BR30-11W-3K	11W LED BR30, 120V, 750LM, DIMMABLE, 3000K
-----------------	--

PAR16

LED-PAR16-6.5W-3K	7W LED PAR16, 120V, 550LM, DIMMABLE, 3000K
-------------------	--

GU10

LED-GU10-6.5W-3K	7W LED GU10, 120V, 550LM, DIMMABLE, 3000K
------------------	---