

R-Series Audio Amplifiers



D250LS 2-Channel Digital Amplifier

Auto-sensing enables localized speaker override for a connected peripheral, such as a TV or PC. The bridgeable power setting combines channel power for 125W into a single 8-ohm load, rated 50W/channel RMS at 8 ohms. 1U 1/2 rack chassis has three mounting options.

Dimensions: 8.5" W x 10.5" D x 1.75" H
(21.59 x 26.67 x 4.45 cm)

Shipping Weight: 10 lbs (4.5 kg)

2800-533280 D250LS
2800-533297 D250LS EU



R290DS 2-Channel Dual Source Amplifier

90W amplifier with auto-source switching. Primary and secondary audio inputs, loop output, selectable speaker level input, and 12V trigger input and output. Rated at 90W/channel into 8 ohms, 110W into 4 ohms, and bridgeable to 250W of power into a single 8 ohm load. Rack ears included.

Dimensions: 17" W x 14" D x 4.125" H
(43 x 35.5 x 10.5 cm)

Shipping Weight: 24.30 lbs (11.02 kg)

2800-530463 R290DS
2800-532719 R290DS EU/UK



R850MC 4 Zone/8 Channel Multiroom Amplifier

Protection circuitry provides safety and reliability under heavy use. Amplifies up to four stereo line-level sources. Zones have dedicated line level inputs or can share a source via the bus input. Separate gain controls for each zone to preset room sound levels. Zone output can be switched to stereo or bridge mono output. In bridged mode, a zone's left and right channels are combined for a higher-power mono output, ideal for large rooms or outdoor listening areas. A+B speaker output in 4 ohm mode. Rack ears included. 50W/channel RMS at 8 ohms x 8.

Dimensions: 17" W x 16.5" D x 5.875" H (43 x 42 x 15 cm)

Shipping Weight 51 lbs (23 kg)

2800-521904 R850MC
2800-532696 R850MC EU/UK



R1250MC 6 Zone/12 Channel Multiroom Amplifier

Zones have dedicated line level inputs or can share a source via the bus input. Separate gain controls for each zone to preset room sound levels. Zone output can be switched to stereo or bridge mono output. In bridged mode, a zone's left and right channels are combined for a higher-power mono output, ideal for large rooms or outdoor listening areas. A+B speaker output in 4 ohm mode. Rack ears included. 50W/channel RMS at 8 ohms x 12.

Dimensions: 17" W x 16.5" D x 5.875" H (43 x 42 x 15 m)

Shipping Weight 61.25 lbs (27.8 kg)

2800-521881 R1250MC
2800-532702 R1250MC EU/UK