

affordable excellence

Share your music anywhere in your home, at the touch of a button. Engineered for elegance and flexibility, the CA4 multizone controller amplifier makes enjoying your music throughout your home an affordable luxury.

For system control, the CA4-KP keypad lets you select between four sources and adjust bass, treble and loudness. It also provides selection for source grouping, all on, all off, and party mode. The keypad features green backlighting, and includes an IR receiver and IR confirmation through an LED status indicator.

For larger homes or individual rooms selected as zones, two CAS44s can be linked together for an eight zone system. Each zone can be supported by up to three keypads for convenience. Your home, your system – endless possibilities.



CA4 Multizone Controller

4 source/4 zone rack mount, source grouping, party mode, fixed and variable line outputs, 1-unit high, 4 zones at 30W/zone, rear RS-232 port, RJ-45 expander jack, 4 single emitters (845.1). Fixed and variable line output (Zone 4 only). Rack ears included.

Shipping Weight: 11 lbs

- 1200-529689 CA4
- 1200-530449 CA4 EU
- 1200-530456 CA4 UK
- 1200-532429 CA4 EU/UK



CA4-WP Wall Port

Single-gang, in-wall port for connection of a CA4 multizone controller to four CA4-KP zone keypads and four pairs of speakers. 4 RJ-45 inputs, 4 RJ-45 keypad outputs, 4 speaker terminal pairs. Wall plates not included.

Shipping Weight: 0.1 oz

1200-529719 CA4-WP White



CA4-RC System Remote Control

Advanced IR learning and pre-programmed remote control for CA4 multizone controller. It is designed to operate source devices and the CA4 multizone audio system keypads. Controls up to four devices.

Shipping Weight: 0.4 oz

1200-529702 CA4-RC



CA4-KT1 Multiroom Controller System Kit

Includes:

- Controller (CA4)
- 4 System Keypads (CA4-KP)
- 4 Emitters (845.1)
- System Remote Control (CA4-RC)
- Pair Rack Ears

Shipping Weight: 14.60 lbs

- 1200-530418 CA4-KT1
- 1200-530425 CA4-KT1 EU
- 1200-530432 CA4-KT1 UK
- 1200-532412 CA4-KT1 EU/UK

EU & UK kits include screwless wallplates



CA4-KP System Keypad

Single-gang, in-wall Decora® style keypad for control of a CA4 multizone audio system. 1 RJ-45 connection. Wall plates not included.

Shipping Weight: 0.1 oz

1200-529696 CA4-KP White



CA4-KP CONV Color Conversion Kit

Includes (4) Decora inserts and 1 wall port insert.

Shipping Weight: 2 oz (.1 kg)

- 1200-531057 CA4-KP CONV White
- 1200-531064 CA4-KP CONV Almond
- 1200-531095 CA4-KP CONV Bone
- 1200-531071 CA4-KP CONV Black
- 1200-531088 CA4-KP CONV Brown

# Speaker Selectors

Speaker selectors are an efficient, cost-effective means of expanding the audio system in your home or office. From four to twelve rooms, with or without volume controls, multiple A/B amplifier inputs to automatic A/B switching devices, Russound speaker selectors can be used to accommodate a number of applications from the simple to sophisticated.

## Single Source Selectors



**SS-4.2** 4 Pair

100W/channel RMS, zone labels. 4 Ω stable amplifiers & receivers. Resettable circuit protection. Impedance bypass switch for use with impedance matching volume controls.

Dimensions:  
8.5" W x 1.875" H x 6.25" D  
(22 x 4.8 x 16 cm)

Shipping Weight: 2.75 lbs  
(1.2 kg)

**3630-520679 SS-4.2**



**SS-6.2** 6 Pair

70W/channel RMS, zone labels. 4 Ω stable amplifiers & receivers. Resettable circuit protection. Impedance bypass switch for use with impedance matching volume controls.

Dimensions:  
11.5" W x 1.875" H x 6.25" D  
(29.5 x 4.8 x 16 cm)

Shipping Weight: 3.5 lbs (1.6 kg)

**3630-520686 SS-6.2**



**SDB-2.1** 2 Pair

100W/channel RMS. Color-coded detachable 14-gauge snap connector. Standard configuration is 4x, and installer may change configuration to 2x or 8x. Zone identifying labels included.

Dimensions:  
8.5" W x 3" H x 6.25" D  
(22 x 8 x 16 cm)

Shipping Weight: 5.5 lbs (2.5 kg)

**3615-604010 SDB-2.1**



**SDB-4.1** 4 Pair

200W/channel RMS. Color-coded detachable 14-gauge snap connectors. Standard configuration is 4x, and installer may change configuration to 2x or 8x. Zone identifying labels included.

Dimensions:  
17" W x 3" H x 6.25" D  
(43.5 x 8 x 16 cm)

Shipping Weight: 2.75 lbs  
(1.2 kg)

**3615-604027 SDB-4.1**



**SDB-6.1** 6 Pair

100W/channel RMS, zone label. 4 Ω stable amplifiers & receivers. Resettable circuit protection. Impedance bypass switch for use with impedance matching volume controls.

Dimensions:  
17" W x 3" H x 6.25" D  
(43.5 x 8 x 16 cm)

Shipping Weight:  
11 lbs (5 kg)

**3615-604034 SDB-6.1**

## Autoformer-Based Selectors/Impedance Matching



**PRO-6 HP** 6 Pair

100W/channel RMS with subsonic filter built in. Color-coded detachable 14-gauge snap connectors. Zone labels included.

Dimensions:  
17" W x 2.875" H x 8" D (43.5 x 7.5 x 20.5 cm)

Shipping Weight: 9.5 lbs (4.3 kg)

**3610-603075 PRO-6 HP**



**PRO-8 HP** 8 Pair

100W/channel RMS with subsonic filter, built in. Color-coded detachable 14-gauge snap connectors. Zone labels included.

Dimensions:  
17" W x 2.875" H x 8" D (43.5 x 7.5 x 20.5 cm)

Shipping Weight: 10 lbs (4.5 kg)

**3610-603136 PRO-8 HP**



**PRO-12 HP** 12 Pair

100W/channel RMS with subsonic filter built in. Color-coded detachable 14-gauge snap connectors. Zone labels included.

Dimensions:  
17" W x 2.875" H x 8" D (43.5 x 7.5 x 20.5 cm)

Shipping Weight: 10 lbs (4.5kg)

**3610-603037 PRO-12 HP**

## Miscellaneous Speaker Selectors



**AB-2.2**  
Tabletop  
Dual-Source

A single pair of speakers to be driven by either of two amplifiers or allow a single amplifier to drive either of two pairs of speakers.

Dimensions:  
5.5" W x 2.875" H x 3" D (140 x 73.5 x 76.5 mm)

Shipping Weight: 1.25 lbs (0.57 kg)

**3699-520525 AB-2.2**



**AB-3.2** Source Selector

Automatic A/B speaker selector, speaker level switching, selectable delay and sensitivity. Color-coded detachable 14-gauge snap connectors. Detachable 12v DC power supply.

Dimensions:  
6.25" W x 2" H x 1.55" D (159 x 51 x 39 mm)

Shipping Weight: 1.7 lbs (0.8 kg)

**3699-520914 AB-3.2**  
**3699-521270 AB-3.2 EU**  
**3699-521287 AB-3.2 UK**



**AB-1.2** Dual-Source

Allows a single pair of speakers to be driven by either of two amplifiers or allow a single amplifier to drive either of two pairs of speakers. Decora® wallplate not included.

Dimensions:  
1" W x 2.75" H x 1.75" D (25.5 x 70 x 44.5 mm)

Shipping Weight: 3 oz (85 g)

**3699-520501 White AB-1.2**    **3699-521294 Brown AB-1.2**  
**3699-520532 Almond AB-1.2**    **3699-521317 Black AB-1.2**  
**3699-520556 Bone AB-1.2**