

CA4 Intermediate System



CA4 Multi-zone Controller



4 source/4 zone rack mountable, source grouping, party mode, 1-U high, 4 zones at 30W/zone, rear RS-232 port, RJ-45 expander jack, 4 single IR emitters. Fixed and variable line output (Zone 4 only). CA4-WP and Rack ears included.

Dimensions:
16.9"W x 2"H x 8.75"D
(43 x 5 x 22.3 cm)

Shipping Weight: 11 lbs (5.0 kg)

1200-529689 CA4
1200-532429 CA4-EU/UK



CA4-KT1 Multi-room Controller System Kit

Includes:

- Controller (CA4)
- 4 System Keypads (CA4-KP)
- Wall Port (CA4-WP)
- 4 IR Emitters
- System Remote Control (USRC)
- Rack Ears
- Wall plates not included

Shipping Weight: 14.60 lbs (6.6 kg)

1200-530418 CA4-KT1
1200-532412 CA4-KT1-EU/UK



CA4-KP System Keypad

Single-gang, in-wall Decora® style keypad for control of a CA4 multi-zone audio system. 1 RJ-45 connection. Wall plate not included.



Dimensions:
1.75"W x 2.875"H x 1.25"D
(45 x 73 x 31.8 mm)

Shipping Weight: 0.2 lbs (0.1 kg)

1200-529696 CA4-KP White



CA4-KP Color Conversion Kit

Includes (4) Decora inserts and 1 wall port insert.

1200-531057 White
1200-534096 Lt Almond
1200-531064 Almond

Shipping Weight: 2 oz (.1 kg)

1200-531095 Bone
1200-531071 Black
1200-531088 Brown



CA4-WP Wall Port

Single-gang, in-wall port for connection of a CA4 multi-zone controller to four CA4-KP zone keypads and four pairs of speakers. 4 RJ-45 inputs, 4 RJ-45 keypad outputs, 4 speaker terminal pairs. Wall plate not included.



Dimensions:
1.75"W x 2.875"H x 1.25"D
(45 x 73 x 31.8 mm)

Shipping Weight: 0.3 lbs (0.1 kg)

1200-529719 CA4-WP White



USRC Universal System Remote Control

The USRC Remote Control is the complete solution for all of your remote control requirements. It is designed to operate source devices and all Russound and A-BUS audio system keypads.



Dimensions:
2"W x 7.75"H x 1.125"D
(5 x 19.7 x 2.9 cm)

Shipping Weight 1 lb (.45 kg)

1700-535000 USRC