




ELECTRONIC / GLASS FUSES



GGX



Glass Body
Fast Acting
1/4" x 1"
1/8A through 2A, 250VAC - UL Listed
1/4A through 2A, 250VAC - CSA Certified
2-1/2A through 5A, 125VAC - UL Listed
and CSA Certified
6A, 125VAC - UL Listed
7A, 125VAC
8A through 30A, 32VAC

Standard Fuse Ampere Ratings

CATALOG NUMBER	AMPERE RATING	VOLTS	I.R.
GGX1/10	1/10A	250V	1
GGX1/8	1/8A	250V	1
GGX1/4	1/4A	250V	1
GGX3/8	3/8A	250V	1
GGX3/16	3/16A	250V	1
GGX1/2	1/2A	250V	1
GGX3/4	3/4A	250V	1
GGX1	1A	250V	1
GGX1-1/2	1-1/2A	250V	2
GGX2	2A	250V	2
GGX2-1/2	2-1/2A	125V	3
GGX3	3A	125V	3
GGX4	4A	125V	3
GGX5	5A	125V	3
GGX6	6A	125V	3
GGX7	7A	125V	3
GGX8	8A	32V	4
GGX10	10A	32V	4
GGX12	12A	32V	4
GGX15	15A	32V	4
GGX20	20A	32V	4
GGX25	25A	32V	4
GGX30	30A	32V	4

1. 250VAC @ 35A I.R./125VAC @ 10kA I.R.
2. 250VAC @ 100A I.R./125VAC @ 10kA I.R.
3. 125VAC @ 10kA I.R.
4. 32VAC

GAB



Ceramic Body
Fast Acting
1/4" x 1-1/4"
1/8A through 15A, 250VAC -
UL Listed and CSA Certified
20A through 30A, 250VAC -
UL Recognized

Standard Fuse Ampere Ratings

CATALOG NUMBER	AMPERE RATING	VOLTS	I.R.
GAB1/8	1/8A	250V	1
GAB1/4	1/4A	250V	1
GAB3/8	3/8A	250V	1
GAB1/2	1/2A	250V	1
GAB3/4	3/4A	250V	1
GAB1	1A	250V	1
GAB2	2A	250V	2
GAB2-1/2	2-1/2A	250V	2
GAB3	3A	250V	2
GAB4	4A	250V	3
GAB5	5A	250V	3
GAB6	6A	250V	3
GAB7	7A	250V	3
GAB8	8A	250V	3
GAB10	10A	250V	3
GAB12	12A	250V	4
GAB15	15A	250V	4
GAB20	20A	250V	5
GAB25	25A	250V	6
GAB30	30A	250V	6

1. 250VAC @ 35A I.R./125VAC @ 10kA I.R.
2. 250VAC @ 100A I.R./125VAC @ 10kA I.R.
3. 250VAC @ 200A I.R./125VAC @ 10kA I.R.
4. 250VAC @ 750A I.R./125VAC @ 10kA I.R.
5. 250VAC @ 1000A I.R./125VAC @ 10kA I.R.
6. 250VAC @ 1000A I.R./125VAC @ 400A I.R.

GSR-V



Epoxy-Coated Body
Fast Acting
7.1mm Body Length
1/16A through 10A, 125VAC -
UL Recognized and CSA Certified
12A & 15A, 32VAC -
UL Recognized and CSA Certified

Standard Fuse Ampere Ratings

CATALOG NUMBER	AMPERE RATING	VOLTS	I.R.
GSR-V1/16	1/16A	125V	1
GSR-V1/8	1/8A	125V	1
GSR-V1/4	1/4A	125V	1
GSR-V3/8	3/8A	125V	1
GSR-V1/2	1/2A	125V	1
GSR-V3/4	3/4A	125V	1
GSR-V1	1A	125V	1
GSR-V1-1/2	1-1/2A	125V	1
GSR-V2	2A	125V	1
GSR-V2-1/2	2-1/2A	125V	1
GSR-V3	3A	125V	1
GSR-V3-1/2	3-1/2A	125V	1
GSR-V4	4A	125V	1
GSR-V5	5A	125V	1
GSR-V7	7A	125V	1
GSR-V10	10A	125V	1
GSR-V12	12A	32V	2
GSR-V15	15A	32V	2

1. 125VAC @ 50A I.R.
2. 32VAC @ 50A I.R.