

ELECTRONIC/GLASS FUSES



GSD / GSD-V

Ceramic Body
Fast Acting
5mm x 20 mm
1-1/2" Axial Leads Optional

1/6A through 10A, 250VAC, UL & CSA Recognized
1A through 6-3/10A, 250VAC, SEMKO Approved
1A through 6-3/10A, 250VAC, VDE Approved
IEC 127-2 Standard Sheet 1*



GSF / GSF-V

Ceramic Body
Time Delay
5mm x 20 mm
1-1/2" Axial Leads Optional

1/2A through 8/10A, 250VAC
1A through 6-3/10A, 250VAC, SEMKO, VDE Approved
1A through 10A, 250VAC, UL and CSA Recognized
IEC-127-2 Standard Sheet 5*

C

Standard Fuse Ampere Ratings

| CATALOG NUMBER | AXIAL LEAD CAT. NO | AMPERE RATING | VOLTS | I.R. |
|----------------|--------------------|---------------|-------|------|
| GSD1/16 | GSD-V1/16 | 1/16A | 250V | 1 |
| GSD8/100 | GSD-V8/100 | 8/100A | 250V | 1 |
| GSD1/10 | GSD-V1/10 | 1/10A | 250V | 1 |
| GSD1/8 | GSD-V1/8 | 1/8A | 250V | 1 |
| GSD16/100 | GSD-V16/100 | 16/100A | 250V | 1 |
| GSD2/10 | GSD-V2/10 | 2/10A | 250V | 1 |
| GSD1/4 | GSD-V1/4 | 1/4A | 250V | 1 |
| GSD315/1000 | GSD-V315/1000 | 315/1000A | 250V | 1 |
| GSD4/10 | GSD-V4/10 | 4/10A | 250V | 1 |
| GSD1/2 | GSD-V1/2 | 1/2A | 250V | 1 |
| GSD630/1000 | GSD-V630/1000 | 630/1000A | 250V | 1 |
| GSD8/10 | GSD-V8/10 | 8/10A | 250V | 1 |
| GSD1 | GSD-V1 | 1A | 250V | 1 |
| GSD1-1/4 | GSD-V1-1/4 | 1-1/4A | 250V | 1 |
| GSD1-6/10 | GSD-V1-6/10 | 1-6/10A | 250V | 1 |
| GSD2 | GSD-V2 | 2A | 250V | 1 |
| GSD2-1/2 | GSD-V2-1/2 | 2-1/2A | 250V | 1 |
| GSD3-15/100 | GSD-V3-15/100 | 3-15/100A | 250V | 1 |
| GSD4 | GSD-V4 | 4A | 250V | 1 |
| GSD5 | GSD-V5 | 5A | 250V | 1 |
| GSD6-3/10 | GSD-V6-3/10 | 6-3/10A | 250V | 1 |
| GSD8 | GSD-V8 | 8A | 250V | 1 |
| GSD10 | GSD-V10 | 10A | 250V | 1 |

1. 250VAC @ 1500A I.R.

* IEC Standards for 5x20mm fuses do not include ratings above 6.3 amperes.

Standard Fuse Ampere Ratings

| CATALOG NUMBER | AXIAL LEAD CAT. NO | AMPERE RATING | VOLTS | I.R. |
|----------------|--------------------|---------------|-------|------|
| GSF1/2 | GSF-V1/2 | 1/2A | 250V | 1 |
| GSF630/1000 | GSF-V630/1000 | 630/1000A | 250V | 1 |
| GSF8/10 | GSF-V8/10 | 8/10A | 250V | 1 |
| GSF1 | GSF-V1 | 1A | 250V | 1 |
| GSF1-1/4 | GSF-V1-1/4 | 1-1/4A | 250V | 1 |
| GSF1-6/10 | GSF-V1-6/10 | 1-6/10A | 250V | 1 |
| GSF2 | GSF-V2 | 2A | 250V | 1 |
| GSF2-1/2 | GSF-V2-1/2 | 2-1/2A | 250V | 1 |
| GSF3-15/100 | GSF-V3-15/100 | 3-15/100A | 250V | 1 |
| GSF4 | GSF-V4 | 4A | 250V | 1 |
| GSF5 | GSF-V5 | 5A | 250V | 1 |
| GSF6-3/10 | GSF-V6-3/10 | 6-3/10A | 250V | 1 |
| GSF8 | GSF-V8 | 8A | 250V | 1 |
| GSF10 | GSF-V10 | 10A | 250V | 1 |

1. 250VAC @ 1500A I.R.

* IEC Standards for 5x20mm fuses do not include ratings above 6.3 amperes.