



Nameplates



Standard Markings

Metal Nameplates And Inserts For Standard Size Plastic Nameplate Holders

Marking	Metal Nameplate Catalog No.	List Price, GO-10GC	Plastic Insert Catalog No. ¹	List Price, GO-10GC
Auto	P9ACP2N219	\$1.80	P9ACPBS219	\$.50
Auto Cut	P9ACP2N272	1.80	P9ACPBS272	.50
Auto Return	P9ACP2N273	1.80	P9ACPBS273	.50
Close	P9ACP2N205	1.80	P9ACPBS205	.50
Control Off	P9ACP2N262	1.80	P9ACPBS262	.50
Control On	P9ACP2N286	1.80	P9ACPBS286	.50
Cycle On	P9ACP2N266	1.80	P9ACPBS266	.50
Decrease	P9ACP2N274	1.80	P9ACPBS274	.50
Down	P9ACP2N203	1.80	P9ACPBS203	.50
Emergency Stop (RED)	P9ACP2R229	1.80	P9ACPBS229	.50
Emergency Stop Pull to Reset (RED)	P9ACP2R230	1.80	P9ACPBS230	.50
Fast	P9ACP2N208	1.80	P9ACPBS208	.50
Fault	P9ACP2N218	1.80	P9ACPBS218	.50
Forward	P9ACP2N214	1.80	P9ACPBS214	.50
Hand	P9ACP2N220	1.80	P9ACPBS220	.50
High	P9ACP2N221	1.80	P9ACPBS221	.50
In	P9ACP2N275	1.80	P9ACPBS275	.50
Inch	P9ACP2N209	1.80	P9ACPBS209	.50
Increase	P9ACP2N278	1.80	P9ACPBS278	.50
Jog	P9ACP2N210	1.80	P9ACPBS210	.50
Left	P9ACP2N222	1.80	P9ACPBS222	.50
Low	P9ACP2N223	1.80	P9ACPBS223	.50
Lower	P9ACP2N217	1.80	P9ACPBS217	.50
Off (Red)	P9ACP2R213	1.80	P9ACPBS213	.50
On	P9ACP2N212	1.80	P9ACPBS212	.50
Open	P9ACP2N206	1.80	P9ACPBS206	.50
Out	P9ACP2N293	1.80	P9ACPBS293	.50
Overload Tripped	P9ACP2N226	1.80	P9ACPBS226	.50
Power On	P9ACP2N240	1.80	P9ACPBS240	.50
Push to Stop/Pull to Start	P9ACP2N241	1.80	P9ACPBS241	.50
Raise	P9ACP2N216	1.80	P9ACPBS216	.50
Reset	P9ACP2N291	1.80	P9ACPBS291	.50
Return	P9ACP2N242	1.80	P9ACPBS242	.50
Reverse	P9ACP2N215	1.80	P9ACPBS215	.50
Right	P9ACP2N224	1.80	P9ACPBS224	.50
Run	P9ACP2N211	1.80	P9ACPBS211	.50
Safe	P9ACP2N281	1.80	P9ACPBS281	.50
Slow	P9ACP2N207	1.80	P9ACPBS207	.50
Spindle Closed	P9ACP2N294	1.80	P9ACPBS294	.50
Spindle Open	P9ACP2N295	1.80	P9ACPBS295	.50
Start	P9ACP2N202	1.80	P9ACPBS202	.50
Stop (RED)	P9ACP2R201	1.80	P9ACPBS201	.50
Stop Rotate to Reset	P9ACP2N228	1.80	P9ACPBS228	.50
Sub SPD Closed	P9ACP2N296	1.80	P9ACPBS296	.50
Sub SPD Open	P9ACP2N297	1.80	P9ACPBS297	.50
Test	P9ACP2N225	1.80	P9ACPBS225	.50
Up	P9ACP2N204	1.80	P9ACPBS204	.50
Feed Hold	P9ACP2N263	1.80	P9ACPBS263	.50
For Rev	P9ACP2N231	1.80	P9ACPBS231	.50
Hand Auto	P9ACP2N243	1.80	P9ACPBS243	.50
High Low	P9ACP2N244	1.80	P9ACPBS244	.50
H.P. Coolant	P9ACP2N290	1.80	P9ACPBS290	.50

¹ For use with plastic nameplate holders on page 38.

Nameplates

Standard Markings

Metal Nameplates And Inserts For Standard Size Plastic Nameplate Holders

Marking	Metal Nameplate Catalog No.	List Price, GO-10GC	Plastic Insert Catalog No. ¹	List Price, GO-10GC
Inch Cut	P9ACP2N276	1.80	P9ACPBS276	.50
Inch Return	P9ACP2N277	1.80	P9ACPBS277	.50
Jog Forward	P9ACP2N279	1.80	P9ACPBS279	.50
Jog Reverse	P9ACP2N280	1.80	P9ACPBS280	.50
Jog Run	P9ACP2N245	1.80	P9ACPBS245	.50
Left Right	P9ACP2N246	1.80	P9ACPBS246	.50
Low High	P9ACP2N247	1.80	P9ACPBS247	.50
Lower Raise	P9ACP2N248	1.80	P9ACPBS248	.50
Off On	P9ACP2N233	1.80	P9ACPBS233	.50
Open Close	P9ACP2N234	1.80	P9ACPBS234	.50
Raise Lower	P9ACP2N249	1.80	P9ACPBS249	.50
Rev For	P9ACP2N250	1.80	P9ACPBS250	.50
Run Jog	P9ACP2N251	1.80	P9ACPBS251	.50
Safe Run	P9ACP2N252	1.80	P9ACPBS252	.50
Slow Fast	P9ACP2N253	1.80	P9ACPBS253	.50
Start Cycle	P9ACP2N282	1.80	P9ACPBS282	.50
Start Feed	P9ACP2N283	1.80	P9ACPBS283	.50
Start Jog	P9ACP2N254	1.80	P9ACPBS254	.50
Start Stop	P9ACP2N255	1.80	P9ACPBS255	.50
Stop Cycle	P9ACP2N265	1.80	P9ACPBS265	.50
Stop Feed	P9ACP2N264	1.80	P9ACPBS264	.50
Stop Reset (Red)	P9ACP2R227	1.80	P9ACPBS227	.50
Stop Start	P9ACP2N232	1.80	P9ACPBS232	.50
Up Down	P9ACP2N256	1.80	P9ACPBS256	.50
Off Coolant On	P9ACP2N257	1.80	P9ACPBS257	.50
Auto Off Hand	P9ACP2N258	1.80	P9ACPBS258	.50
For Off Rev	P9ACP2N239	1.80	P9ACPBS239	.50
For Stop Rev	P9ACP2N259	1.80	P9ACPBS259	.50
Hand Off Auto	P9ACP2N261	1.80	P9ACPBS261	.50
Jog Off Run	P9ACP2N298	1.80	P9ACPBS298	.50
Jog Safe Run	P9ACP2N267	1.80	P9ACPBS267	.50
Local Off Remote	P9ACP2N237	1.80	P9ACPBS237	.50
Low Off High	P9ACP2N238	1.80	P9ACPBS238	.50
Lower Off Raise	P9ACP2N268	1.80	P9ACPBS268	.50
Man Off Auto	P9ACP2N269	1.80	P9ACPBS269	.50
Open Off Close	P9ACP2N270	1.80	P9ACPBS270	.50
Slow Off Fast	P9ACP2N271	1.80	P9ACPBS271	.50
Abrir	—	—	P9ACPBS506	.50
Adelante	—	—	P9ACPBS502	.50
Atras	—	—	P9ACPBS508	.50
Atras Adelante	—	—	P9ACPBS518	.50
Atras O Adelante	—	—	P9ACPBS519	.50
Bajar	—	—	P9ACPBS505	.50
Bajo	—	—	P9ACPBS514	.50
Cerrar	—	—	P9ACPBS501	.50
Defecto	—	—	P9ACPBS513	.50
Derecha	—	—	P9ACPBS509	.50
Emergencia	—	—	P9ACPBS516	.50
Izquierda	—	—	P9ACPBS504	.50
Manual	—	—	P9ACPBS503	.50
Marcha	—	—	P9ACPBS510	.50
Paro (Red)	—	—	P9ACPBS511	.50
Paro Marcha	—	—	P9ACPBS517	.50
Paro O Marcha	—	—	P9ACPBS520	.50
Rapido	—	—	P9ACPBS512	.50
Rearme	—	—	P9ACPBS515	.50
Subir	—	—	P9ACPBS507	.50

¹ For use with plastic nameplate holders on page 38.