

Safety Switches Heavy Duty, Type TH

Spec-Setter™ Safety Switches

30-1200 Amperes

240, 480, 600 Volts AC

600 Volts DC

Section 2

Two-pole, 600 Volts DC, No Fuse

Ampere Rating	Enclosure Type	HP, 240 Vac, NEC Std, 1-ph	HP, 240 Vac, NEC Std, 3-ph	HP, 480 Vac, Time Delay, 3-ph	HP, 600 Vac, Time Delay, 3-ph	HP, 125 Vdc	HP, 250 Vdc	HP, 600 Vdc	Product Number	List Price GO-131
30A	NEMA Type 1	–	–	–	–	–	–	15	THN2261DC	\$179.00
60A	NEMA Type 1	–	–	–	–	–	–	25	THN2262DC	\$324.00
100A	NEMA Type 1	–	–	–	–	–	–	25	THN2263DC	\$510.00
30A	NEMA Type 3R	–	–	–	–	–	–	15	THN2261RDC	\$322.00
60A	NEMA Type 3R	–	–	–	–	–	–	25	THN2262RDC	\$564.00
100A	NEMA Type 3R	–	–	–	–	–	–	25	THN2263RDC	\$788.00
30A	NEMA Type 4/4X	–	–	–	–	–	–	15	THN2261SSDC	\$1300.00
60A	NEMA Type 4/4X	–	–	–	–	–	–	25	THN2262SSDC	\$1562.00
100A	NEMA Type 4/4X	–	–	–	–	–	–	25	THN2263SSDC	\$3216.00
30A	NEMA Type 5, 12	–	–	–	–	–	–	15	THN2261JDC	\$352.00
60A	NEMA Type 5, 12	–	–	–	–	–	–	25	THN2262JDC	\$397.00
100A	NEMA Type 5, 12	–	–	–	–	–	–	25	THN2263JDC	\$632.00

Three-pole, 480 and 600 Volts AC - 250 Volts DC or Two-pole with Switching Neutral, No Fuse

Ampere Rating	Enclosure Type	HP, 240 Vac, NEC Std, 1-ph	HP, 240 Vac, NEC Std, 3-ph	HP, 480 Vac, Time Delay, 3-ph	HP, 600 Vac, Time Delay, 3-ph	HP, 125 Vdc	HP, 250 Vdc	HP, 600 Vdc	Product Number	List Price GO-131
30A	NEMA Type 1	3	10	–	–	3	5	–	THN3321 ¹	\$171.00
30A	NEMA Type 1	3	10	20	30	3	5	–	THN3361	\$179.00
60A	NEMA Type 1	10	20	50	60	5	10	–	THN3362	\$324.00
100A	NEMA Type 1	20	40	75	100	–	20	–	THN3363	\$510.00
200A	NEMA Type 1	30	60	125	150	–	40	–	THN3364	\$775.00
400A	NEMA Type 1	–	125	250	350	–	50	–	THN3365	\$1736.00
600A	NEMA Type 1	–	200	400	500	–	50	–	THN3366	\$3092.00
800A	NEMA Type 1	–	–	–	–	–	–	–	TC36367 ^{2,3}	\$6302.00
1200A	NEMA Type 1	–	–	–	–	–	–	–	TC36368 ^{2,3}	\$8457.00
30A	NEMA Type 3R	3	10	20	30	3	5	–	THN3361R	\$322.00
30A	NEMA Type 3R	3	10	20	30	3	5	–	THN3361RF ⁴	\$436.00
60A	NEMA Type 3R	10	20	50	60	5	10	–	THN3362R	\$564.00
60A	NEMA Type 3R	10	20	50	60	5	10	–	THN3362RF ⁴	\$564.00
100A	NEMA Type 3R	20	40	75	100	–	20	–	THN3363R	\$788.00
200A	NEMA Type 3R	30	60	125	150	–	40	–	THN3364R	\$957.00
400A	NEMA Type 3R	–	125	250	350	–	50	–	THN3365R	\$2376.00
600A	NEMA Type 3R	–	200	400	500	–	50	–	THN3366R	\$4755.00
30A	NEMA Type 4/4X	3	10	20	30	3	5	–	THN3361SS	\$1326.00
60A	NEMA Type 4/4X	10	20	50	60	5	10	–	THN3362SS	\$1577.00
100A	NEMA Type 4/4X	20	40	75	100	–	20	–	THN3363SS	\$3217.00
200A	NEMA Type 4/4X	30	60	125	150	–	40	–	THN3364SS	\$4393.00
400A	NEMA Type 4/4X	–	125	250	350	–	50	–	THN3365SS	\$8899.00
600A	NEMA Type 4/4X	–	200	400	500	–	50	–	THN3366SS	\$11946.00
30A	NEMA Type 5, 12	3	10	20	30	3	5	–	THN3361J	\$412.00
60A	NEMA Type 5, 12	10	20	50	60	5	10	–	THN3362J	\$533.00
100A	NEMA Type 5, 12	20	40	75	100	–	20	–	THN3363J	\$758.00
200A	NEMA Type 5, 12	30	60	125	150	–	40	–	THN3364J	\$1008.00
400A	NEMA Type 5, 12	–	125	250	350	–	50	–	THN3365J	\$2497.00
600A	NEMA Type 5, 12	–	200	400	500	–	50	–	THN3366J	\$4065.00

For Type 1 Enclosure: 200-600 amp devices available factory reversed for bottom feed. Add "B" suffix to product number (e.g., TH33365B). **List Price adder \$44.00, GO-131.**
UL Listed.

For Type 3R Enclosure: 30-200 amp devices have removable closing cap. Order hubs for these devices separately on page 2-28. Larger amp devices require field cut openings and **customer-supplied** hub.

Use molded case switch in circuit breaker enclosure.

¹250 volts AC or 250 volts DC only. Compact enclosure.

²Class "L" fuses are only applicable when used with 800 and 1200A Type TC Safety Switches (e.g. TC72367).

³Not available with neutral.

⁴RF-version provides for vertically-hinged NEMA 3R door.



Publications and Reference: See Section 22 for a complete list of additional product-related publications