

Residential Load Centers

Section 1

Page Updated 05 / 2008

PowerMark Gold and Plus Main Breaker Load Centers

Main Breaker Factory Installed

Single-Phase, Three-Wire, 120/240 Vac, Main Breaker Factory Installed

Indoor (NEMA 1) Enclosure

Main Ampere Rating	1 Pole, 1" Spaces	2 Pole, 1" Spaces	1 Pole, 1/2" Spaces	2 Pole, 1/2" Spaces	Total 1-pole Spaces	Front Type	Feed Type	Box Number	Main Wire Size (AWG/kcmil) Cu-Al	Equipment Ground Kit	Product Number	List Price GO-137D
200	14	8	32	14	32	Combination Flush/Surface Front	Top Bottom	8	1-250 (Cu), 2/0-250 (Al)	TGK32 installed	TM1620CCUG	\$517.00
200	18	10	40	18	40	Combination Flush/Surface Front	Top Bottom	8	1-250 (Cu), 2/0-250 (Al)	TGK24 (order separately) TGK42 (order separately)	TM2020CCU	\$544.00
200	18	10	40	18	40	Combination Flush/Surface Front	Top Bottom	8	1-250 (Cu), 2/0-250 (Al)	TGK42 installed	TM2020CCUG	\$568.00
200	32	16	16	6	40	Combination Flush/Surface Front	Top Bottom	11	1-250 (Cu), 2/0-250 (Al)	TGK32 (order separately)	TM3220CCU	\$663.00
200	40	20	0	0	40	Combination Flush/Surface Front	Top Bottom	13	1-250 (Cu), 2/0-250 (Al)	TGK42 (order separately)	TM4020CCU	\$776.00
200	24	12	36	18	42	Combination Flush/Surface Front	Top Bottom	9	1-3/0 (Cu), 2/0-3/0 (Al)	TGK24 or TLK32 (order separately)	TM2420C42	\$750.00
200	32	16	20	10	42	Combination Flush/Surface Front	Top Bottom	11	1-250 (Cu), 2/0-250 (Al)	TGK32 and TLK20 (order separately)	TM3220C42	\$776.00
200	42	20	0	0	42	Combination Flush/Surface Front	Top Bottom	14	1-300 (Cu), 2/0-300 (Al)	TGK42 (order separately)	TM4220CCU	\$850.00
225	42	20	0	0	42	Combination Flush/Surface Front	Top Bottom	14	1-300 (Cu), 2/0-300 (Al)	TGK42 (order separately)	TM4222CCU	\$852.00

Single-Phase, Three-Wire 120/240 Vac Main Breaker Factory Installed

Outdoor (NEMA 3R) Enclosure¹

Main Ampere Rating	1 Pole, 1" Spaces	2 Pole, 1" Spaces	1 Pole, 1/2" Spaces	2 Pole, 1/2" Spaces	Total 1-pole Spaces	Feed Type	Box Number	Main Wire Size (AWG/kcmil) Cu-Al	Equipment Ground Kit	Product Number	List Price GO-137D
100	12	6	24	10	24	Top	R3	4-1/0	TGK12 (order separately) TGK24 (order separately)	TM1210RCU	\$357.00
100	20	10	0	0	30	Top	R4	4-1/0	TGK24 (order separately)	TM2010RCU	\$385.00
125	12	12	24	10	24	Top	R4	1-2/0	TGK12 (order separately) TGK24 (order separately)	TM1212RCU	\$512.00
125	24	12	0	0	24	Top	R4	1-2/0	TGK24 (order separately)	TM2412RCU	\$601.00
150	8	4	16	6	16	Top	R5	1-250 (Cu), 2/0-250 (Al)	TGK24 (order separately)	TM815RCUFL	\$656.00
150	16	8	32	14	32	Top	R5	1-3/0 (Cu), 2/0-3/0 (Al)	TGK24 (order separately) TGK32 (order separately)	TM1615RCU	\$594.00
150	24	12	12	4	30	Top	R6	1-3/0 (Cu), 2/0-3/0 (Al)	TGK24 (order separately) TGK32 (order separately)	TM2415RCU	\$732.00
150	24	12	36	18	42	Top Bottom	R39	1-250 (Cu), 2/0-250 (Al)	TGK24 (order separately)	TM2415R42B	\$800.00
150	32	16	0	0	32	Top	R7	1-3/0 (Cu), 2/0-3/0 (Al)	TGK32 (order separately)	TM3215RCU	\$743.00
200	8	4	16	6	16	Top	R5	1-250 (Cu), 2/0-250 (Al)	TGK32 (order separately)	TM820RCUFL	\$654.00
200	20	10	40	18	40	Top	R6	1-250 (Cu), 2/0-250 (Al)	TGK24 (order separately) TGK42 (order separately)	TM2020RCU	\$629.00
200	24	12	36	18	42	Top Bottom	R39	1-250 (Cu), 2/0-250 (Al)	TGK24 (order separately)	TM2420R42B	\$855.00
200	32	16	16	6	40	Top	R7	1-250 (Cu), 2/0-250 (Al)	TGK32 (order separately)	TM3220RCU	\$798.00
200	40	20	0	0	40	Top	R8	1-250 (Cu), 2/0-250 (Al)	TGK42 (order separately)	TM4020RCU	\$924.00
225	8	4	16	6	16	Top	R5	1-250 (Cu), 2/0-250 (Al)	TGK24 (order separately)	TM822RCUFL	\$774.00
225	42	20	0	0	42	Top	R8	1-300 (Cu), 2/0-300 (Al)	TGK42 (order separately)	TM4222RCU	\$962.00

¹100-225 amp devices have removable closing caps. Larger ampere devices require field-cut openings. Order hubs separately. See page 1-27.

Note: See page 9-15, AL Series Lighting Panelboards as replacements for 300-600A load centers.



Publications and Reference: See Section 22 for a complete list of additional product-related publications