IC20R 5" Incandescent Remodel Housing

juno

IP.LOC

Features

- 5" Remodel housing
- Drop socket with spring to accommodate various trim installations
- Medium base porcelain socket with nickel-plated copper screw shell
- Remodel springs accommodate up to a 1 1/8" ceiling thickness
- Housing is fully assembled for ease of installation
- Pre-wired junction box with (5) 1/2" knockouts with pryout slots, (4) Romex[™] connectors, and ground wire
- Shadow-free, knife-edge trim design blends smoothly into the ceiling and allows architectural continuity with Aculux[™] trims
- UL Listed, C-UL/CSA certified for through-branch wiring, maximum (4) #12 AWG branch circuit conductors (2 in, 2 out)
- Thermally protected against improper use of lamps
- Lamp wattage ratings and apertures based on trim selection on pages 42-43



Description

IC rated, energy efficient Air-Loc® sealed remodel housing for applications where the back side of the ceiling is not accessible • Can be completely covered with insulation • Air-Loc installation stops infiltration and exfiltration of air, reducing heating and cooling costs

Listings

UL Listed, C-UL/CSA certified for through-branch wiring, damp and wet locations • Wet location listed with the 210, 211, and 212 trims • The listing also includes the 215 and 216 trims, only when used with PAR30 outdoor rated lamps • Washington State IECC and MEC energy codes as tested per ASTM-E283 • Conforms with City of Chicago IP requirements


Ordering Information


Catalog Number: IC20R

Accessories

10000001100	
Catalog Number	Description
ALG5R	Air-Loc [®] Energy Conserving
	Gasket Kit for 5" Air-Loc [®] IC
	Remodel housings
SMPLT-5	Galvanized steel plate for
	locating remodel style
	housings in new construction.
	Screw/nail holes for full
	coverage between 16" and
	24" joists.

Dimensions





5 1/2" Ceiling Cutout

JUNO LIGHTING GROUP