

JUNO® lighting

TRAC-LITES UNIVERSAL R541

Project: _____

Fixture Type: _____

Location: _____

Contact/Phone: _____

PRODUCT DESCRIPTION

Construction Drawn steel housing with steel yoke.

Aiming 90° vertical aiming capability and 358° rotation

Socket Medium base porcelain socket with nickel plated copper screw shell.

Adaptor Copper alloy contacts provide precise spring action • True, positive electrical ground • On/off switch included • Patented embossed polarity arrows on bottom of adaptor • Spring-loaded locking latch with embossed polarity arrows secures trac light to trac • "Pull-up" contact to up position for use on two-circuit trac.

Labels UL/CUL listed.



Line Voltage Universal

Catalog Number	Finish	Lamp
R541WH	White	50W PAR20 to 75W PAR30
R541BL	Black	50W PAR20 to 75W PAR30

