



# SUPER SLOPE CEILING IC HOUSING

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact/Phone: \_\_\_\_\_

SUPER SLOPE:

7/12 to 12/12 PITCH (30° to 45°)

INCANDESCENT LAMPS

**IC928**

## PRODUCT DESCRIPTION

Slope ceiling IC Housing "Air-Loc™" • Energy efficient, sealed inner housing • Double wall housing construction • Can be completely covered with insulation • When used with Air-Loc Gasket (see accessories), stops infiltration and exfiltration of air, reducing heating and cooling costs.

## PRODUCT SPECIFICATIONS

**Lamp** Lamp ratings based on trim selected – see reverse.

**Socket** Medium base porcelain with nickel-plated copper screw shell • Adjustable to position lamp perpendicular to floor.

**Trims** Trim selection shown on reverse.

**Labels** U.L. listed for through-branch wiring, damp locations and IP • Product thermally protected against improper use of lamps • Union made AFL-CIO • UL Listed/CSA certified • Trim No. 603 is wet location approved for covered ceiling applications.

**Testing** All reports are based on published industry procedures; field performance may differ from laboratory performance.

Product specifications subject to change without notice.

## INSTALLATION

**Real Nail 3 Bar Hangers** Telescoping, patent-pending Real Nail 3 system permits quick placement of housing anywhere within 24" O.C. joists or suspended ceilings • Integral T-bar notch and clip secures housing in suspended ceiling grid – no accessory clips required • 24" expansion stop allows quick placement of fixture in standard grid spacing • Bars scored in two locations for fast, clean breaking, allowing housing installation in tight applications • Bars captive to mounting frame • Edge-mounted for extra strength • Captive bugle-headed ring shank nail for quick one-step installation and easy removal with claw hammer for fixture relocation • Quick-Loc slot and oversized locking set screw lock fixture in position • Bar hanger foot contoured to align to bottom of construction joist • Alternate mounting holes included.

**Junction Box** Pre-wired junction box provided with (5) ½" and (1) ¾" knockouts, (4) Non-metallic sheathed cable connectors and ground wire, U.L. listed/CSA certified for through-branch wiring, maximum 8 No. 12 AWG 90° C branch circuit conductors (4 in, 4 out) • Junction box provided with removable access plates • Knockouts equipped with pryout slots.



**Mounting Frame** 22-gauge die-formed galvanized steel mounting frame • Rough-in section (junction box, mounting frame, housing and bar hangers) fully assembled for ease of installation.

**Housing** IC housing, .032" aluminum sealed for Air-Loc Compliance • Access door for junction box accessibility • Housing is vertically adjustable to accommodate up to a 1" ceiling thickness.

## PRODUCT CODES

Catalog Number	Input Voltage	Lamp Rating (max.)
IC928	120V	PAR16/PAR30/PAR38

## DIMENSIONS



## ACCESSORIES

Catalog No.	Description
ALG928	Air-Loc Gasket

To order, specify catalog number.

# SUPER SLOPE CEILING IC HOUSING





SUPER SLOPE:

7/12 to 12/12 PITCH (30° to 45°)

INCANDESCENT LAMPS

**IC928**

## TRIMS/LAMPS

	Cat. No.	Description	Lamp Rating
	<b>602C-WH</b>	Multiplier Cone - Clear Alzak®	75W PAR30, 90W PAR38, 85W BR30
	<b>602G-WH</b>	Multiplier Cone - Gold Alzak®	
	<b>602B-WH</b>	Multiplier Cone - Black Alzak®	
	<b>602HZ-WH</b>	Multiplier Cone - Haze	
	<b>602HZ-SC</b>	Multiplier Cone - Haze	
	<b>602W-WH</b>	Multiplier Cone - White	
	<b>602WHZ-WH</b> <b>602WHZ-ABZ</b>	Multiplier Cone - Wheat Haze Multiplier Cone - Wheat Haze	
	<b>603B-WH</b> ◆	Lensed Shower Trim with Black Baffle	50W PAR30
	<b>603W-WH</b> ◆	Lensed Shower Trim with White Baffle	
	<b>604B-WH</b>	Downlight with Black Baffle	90W PAR38
	<b>604B-SC</b>	Downlight with Black Baffle	
	<b>604B-ABZ</b>	Downlight with Black Baffle	
	<b>604B-BL</b>	Downlight with Black Baffle	
	<b>604W-WH</b>	Downlight with White Baffle	
	<b>606B-WH</b>	Black Cylinder Spotlight with Black Baffle	60W PAR16
	<b>606W-WH</b>	White Cylinder Spotlight with White Baffle	

Trim Size: Cat. No. 604 - 9<sup>7</sup>/<sub>16</sub>" x 8<sup>3</sup>/<sub>16</sub>" O.D., Cat. No. 606 - 9<sup>1</sup>/<sub>8</sub>" O.D.

Trim Finish: ABZ - Classic Aged Bronze, BL - Black, GP - Graphite,

PW - Plastic White (Polycarbonate material shower trim), SC - Satin Chrome, SL - Silver, WH - White.

Note: In Canada when insulation is present, Type IC fixtures must be used.

◆ UL Listed for use in wet location.