

DRILL ACCESSORIES

AUGER BITS, SHIP AUGER BITS, ELECTRICIANS' BITS, BELLHANGER BITS, CABLE BITS

More Economical Ways of Extending the Useful Range of Portable Drills.



SHANK	DIAMETER	CATALOG NUMBER	OVERALL LENGTH	FOR STD. PIPE SIZES
7/16"	3/4"	48-13-0750	6-1/2"	PIPE SIZES
7/16"	7/8"	48-13-0870	6-1/2"	3/8"
7/16"	1"	48-13-1000	6-1/2"	
7/16"	1-1/8"	48-13-1120	6-1/2"	1/2"
7/16"	1-1/4"	48-13-1250	6-1/2"	3/4"
7/16"	1-3/8"	48-13-1370	6-1/2"	
7/16"	1-1/2"	48-13-1500	6-1/2"	1"

HEAVY-DUTY AUGER BITS

4" TWIST 6-1/2" OVERALL LENGTH

Sizes from 3/4" to 1-1/2"...All 4" twist and 6-1/2" long. 7/16" hex shanks for sure chuck grip. Feed screw pilot draws bit into wood. Sharp cutting spurs and lips can be quickly resharpened for fast, efficient production.



15" TWIST 18"

18" OVERALL LENGTH

HEAVY-DUTY SHIP AUGER BITS

For all types of construction. Precision machined for smooth, wobble free boring. Large, wide throat design gives excellent chip clearance from deep holes. Self feeding screwpoint, with one cutting edge and side lip for fast, rough boring in wood. Hardened cutting edges require less resharpening. 1/2" D-Handle drills and larger can use all 1/2" shank bits.

Also in 4" Twist and 6" Overall Length

SHANK	DIA.	CATALOG NUMBER	OVERALL LENGTH
1/2"	11/16"	48-13-0683	6"
1/2"	3/4"	48-13-0753	6"
1/2"	13/16"	48-13-0813	6"
1/2"	7/8"	48-13-0873	6"
1/2"	15/16"	48-13-0933	6"
1/2"	1"	48-13-1003	6"
1/2"	1-1/16"	48-13-1063	6"
1/2"	1-1/8"	48-13-1123	6"
1/2"	1-1/4"	48-13-1253	6"
1/2"	1-3/8"	48-13-1373	6"
1/2"	1-1/2"	48-13-1503	6"

9/16"	48-13-5560	18"
5/8"	48-13-5620	18"
11/16"	48-13-5680	18"
3/4"	48-13-5750	18"
13/16"	48-13-5810	18"
7/8"	48-13-5870	18"
15/16"	48-13-5930	18"
1"	48-13-6000	18"
1-1/16"	48-13-6010	18"
1-1/8"	48-13-6120	18"
1-1/4"	48-13-6250	18"
1-3/8"	48-13-6370	18"
1-1/2"	48-13-6500	18"
	5/8" 11/16" 3/4" 13/16" 7/8" 15/16" 1" 1-1/16" 1-1/4" 1-3/8"	5/8" 48-13-5620 11/16" 48-13-5680 3/4" 48-13-5750 13/16" 48-13-5810 7/8" 48-13-5870 15/16" 48-13-5930 1" 48-13-6000 1-1/16" 48-13-6010 1-1/8" 48-13-6120 1-1/4" 48-13-6250 1-3/8" 48-13-6370

DIAMETER	CATALOG NUMBER	OVERALI LENGTH
5/8"	48-13-8062	8-1/2"
11/16"	48-13-8068	8-1/2"
3/4"	48-13-8075	8-1/2"
13/16"	48-13-8081	8-1/2"

DIAMETER	CATALOG NUMBER	OVERALL LENGTH
7/8"	48-13-8087	8-1/2"
1"	48-13-8100	8-1/2"
1-1/8"	48-13-8112	8-1/2"
1-1/4"	48-13-8125	8-1/2"

HEAVY-DUTY ELECTRICIANS' BITS



A fast spiral, two flute — six inch twist, self feeding bit with an overall length of 8-1/2" for any tradesman needing a smooth, clean hole 5/8" to 1-1/4". 5/8" to 1" diameter bits have a 5/16" hex shank and 1-1/8" to 1-1/4" diameter bits have a 7/16" hex shank.



HEAVY-DUTY BELLHANGER BITS

For installers of all types of small wire systems – computer, security, phone cable, etc. Extra length for extra reach. Pull the wire back through the hole by simply attaching a line or the wire to the bit.



HEAVY-DUTY CABLE BITS

Also for installers of small wire systems. Cable Bits are flexible steel shaft bits in 54" and 72" lengths that let you reach unreachable areas behind walls with greater ease and precision. Use of the placement tool accessory is recommended for setting the bit into proper drilling location within the interior of walls.

PLACEMENT GUIDE TOOL

48-08-0275 Includes instructions.

