



Site Search

News Room

About Lutron

Home

Part-number Search

Careers

Contact Us

Seminars

Home Lighting Control

Commercial Lighting Control

Products

Service & Support

Where to Buy

Technical Info

# Maestro® | Multi-location Dimmers with Designer Styling.

[What Is Maestro?](#) [New Maestro Wireless®](#) [Products](#) [Technical Info](#)

[Maestro Timers](#)

[Maestro >> Products >> Maestro Timers](#)

Timer Only Controls  
Dimmer/Timer Control

Customer Service  
1.888.LUTRON1  
8AM-8PM EST

Technical Assistance  
1.800.523.9466  
24 hours a day,  
7 days a week

Request:  
Printed Literature  
Sales Contact



Maestro Timer

[Click here](#) to learn about Maestro timer features and benefits.

Listed; Lutron controls are rated at 120VAC, 60Hz unless otherwise noted.

Available in 7 gloss and 20 satin colors



Maestro Dimmer/Timer



[Click to learn more](#)

[Online Tech Support](#)

## Timer Only Controls







[Return to Top](#)

Model Number		Control Type	Maximum Capacity	Wiring
Boxed	Clamshell			
MA-T51-	MA-T51HW-WH (white only) wallplate included	single pole	5A lighting load (incandescent or MLV only) or 3A general purpose fan	no neutral required
MA-T51MN-	-	multi-location	5A lighting load or 3A general purpose fan	neutral required



## available models

---

### source type

-  incandescent lighting
-  magnetic low voltage lighting
-  electronic low voltage lighting
-  fluorescent lighting
-  quiet 7-speed fan controls
-  quiet 7-speed fan/light controls

### control locations

-  single pole
-  multi-location

## available colors

---




### colors (gloss finish)

- |                        |                 |
|------------------------|-----------------|
| <b>WH</b> white        | <b>GR</b> gray  |
| <b>IV</b> ivory        | <b>BR</b> brown |
| <b>AL</b> almond       | <b>BL</b> black |
| <b>LA</b> light almond |                 |

### colors (satin finish)

- |                        |                     |
|------------------------|---------------------|
| <b>HT</b> hot          | <b>SG</b> sea glass |
| <b>MR</b> merlot       | <b>SI</b> sienna    |
| <b>TC</b> terracotta   | <b>MN</b> midnight  |
| <b>GB</b> greenbriar   | <b>TP</b> taupe     |
| <b>BG</b> bluestone    | <b>ES</b> eggshell  |
| <b>DS</b> desert stone | <b>BI</b> biscuit   |
| <b>ST</b> stone        | <b>SW</b> snow      |
| <b>LS</b> limestone    |                     |

### colors & finishes key

-  available in gloss finish
-  available in satin finish
-  available in all gloss and satin finishes

See page 17 for color swatches.