

# Code•Master™ LED Factory Sealed Luminaires

## Explosionproof, Dust-Ignitionproof

**NEC/CEC:**

Class I, Division 1 and 2, Groups B, C, D ★  
 Class I, Zone 1, Groups IIA, IIB, IIB + H<sub>2</sub>  
 Class II, Division 1, Group E, F, G  
 Class II, Division 2, Group F, G







**NEC/CEC:**

Class III  
 Simultaneous Exposure  
 Type 3R, 4X  
 IP66/67

**NEC/CEC:**

Suitable for Use in Wet Locations  
 Marine Outside Type (Salt Water) ★

**Accessories and Replacement Parts**

	Description	Catalog Number
<b>Fuse Kits ★</b>		
	3 Amp for 120-277 Vac (BU version), 70 thru 250 Watt Equivalent	<b>CMLEDF-3</b>
	5 Amp for 120-277 Vac (BU version) and 347-480 Vac (BH version), 400 thru 1000 Watt Equivalent	<b>CMLEDF-5</b>
	2 Amp for 347-480 Vac (BU version), 70 thru 350 Watt Equivalent	<b>CMLEDF-2</b>
<b>Globes and Gaskets</b>		
	Clear Globe Assembly	<b>CGL-CLEAR</b>
	Diffused Globe Assembly	<b>CGL-DIFF</b>
	Stainless Steel Wire Guard	<b>CMLEDGU</b>
	Safety Cable	<b>CMLEDSC</b>
	Yoke Bracket	<b>CMLEDYOKE</b>

★ Complete Code•Master LED luminaire consists of fixture unit and a mounting hood. For Group B applications a Group B rated mounting hood must be used.  
 ★ Use of a fuse voids Marine Outside Type (Salt Water) rating.